

5"
Straight Flat
Fluted w/3"
tenon

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Order guide

example: P5065 12 A T D

Product Code	Pole Height	Finish	Outlet Location	Outlet Options
P5065				
P5065	12' 14' 16' 18'	A Black B White G Verde H Bronze I Gray J Green	T 12" Down from Top - Aligned with House Side B 4" Up from Top of Base - Aligned with House Side	D Standard Duplex G GFI Duplex

EPA values based on destructive break testing. For AASHTO ratings, contact factory.

Pole Data

Pole Model	Pole Shape	Pole Type	Shaft Dimension	Pole Fluted	Anchor Base Shape	Bolt Circle	Base Dim (in)	Hand Hole Dim (in)
P5065	Round	Straight	5	Fluted	round	8 to 13	17 x 21	4.5 x 5

Pole Family	Catalog Number	Nominal Height (ft)	Tenon Section (in)	Wall Thickness (in)	EPA Rating 80 MPH (sq. ft)	EPA Rating 100 MPH (sq. ft)	Anchor Bolts (in)
P5065	P5065-12	12	3	0.188 - 0.267	28.22	16.70	3/4-19 bs
P5065	P5065-14	14	3	0.188 - 0.267	19.29	11.26	3/4-19 bs
P5065	P5065-16	16	3	0.188 - 0.267	16.00	8.89	3/4-19 bs
P5065	P5065-18	18	3	0.188 - 0.267	13.99	7.60	3/4-19 bs

Specifications

HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy. 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel. Tenon is 356 HM sand cast aluminum.

FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:

Please visit www.signify.com/warranties for more details on structural and finish warranty.

CERTIFICATIONS:


Manufactured to ISO 9001:2008 Standards.

OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

P5065 Poles and Brackets

Straight Round Fluted



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

