EU Declaration of Conformity

Document No.: 2024M09_V2/LVD
Year in which CE Mark was first affixed*: 2024*

1. Product Range / Model:

Product Range / Model:	**NAME:** Pendant Cloak **DESCRIPTION:** Suspended Luminaires with Edison Screw lampholder (E27) **BRAND**: PHILIPS or SIGNIFY

2. Manufacturer Name & Address:

Signify
I.B.R.S./C.C.R.I. /Numéro 10461
5600 VB Eindhoven, The Netherlands

3. This declaration of conformity is issued under the sole responsibility of the manufacturer.

4. Object of the declaration:

Product Code:	**XXPL00 A B C D E F E27 N G** See Annex for full description

5&6. The object of the declaration described above is in conformity with the following relevant Union harmonization legislation and with the applicable requirements of the following harmonized standards and technical specifications:

Low Voltage Directive (LVD), 2014/35/EU
• EN IEC 60598-1:2021, EN IEC 60598-1:2021/A11:2022 • EN 60598-2-1:1989, EN 60598-2-1:2021

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU and applicable Delegated Directives
• EN IEC 63000:2018

7. Additional information: The product(s) in this declaration are produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

Eindhoven, 09-01-2025
Signify Business 3D Printing
High Tech Campus 26, 5656 AE
Eindhoven, The Netherlands

Yves Diels
Quality Manager
3D Printing

EU Declaration of Conformity

Document No.: 2024M09_V2/LVD

ANNEX

Product naming key XPL00 A B C D E F E27 N G

Where:

X=	Market specific prefix		two characters, may be
	MC	for My Creation	
	TC	for Telecaster	
A=	Size		one character, may be
	S	for small	
B=	Housing Color		upto five characters
	color abbreviation of released material		
C=	Housing Texture		upto 4 characters
D=	Cable Color		two characters, may be
	BK	for Black	
	WH	for White	
E=	Mounting Type		one character, may be
	S	for product with canopy	
	T	for product with track adapter	
F=	Canopy Color or Track Color		upto five characters, may be
	color abbreviation of released material (for Canopy version)		
	WH	for white track	
	BK	for Black track	
G=	Option for commercial suffix		

Max. Power, Ambient Temperature, and IP rating of the series:

Mounting	Max. Power Rating (W)	Max. Ambient Temp (°C)	Ingress Protection
S and T	11W	35	IP20

---End of Annex---