



SFC canopy/ceiling luminaire

# Architecturally cohesive

**Gardco SlenderForm LED luminaires** provide a complete set of LED solutions for every site lighting desire and need. Defined by its high performance, sleek low profile design and rugged construction, whether used under outdoor canopies, on exterior ceilings or in parking garages, the SlenderForm LED canopy luminaire brings exquisite style to an otherwise ordinary environment. Its slim profile and distinctive twin reveals allow the unit to effortlessly complement its surroundings. Utilizing the SlenderForm family, the entire look of the site can be integrated to provide an architecturally diverse yet unified appearance.

## Benefits

- Provides precise illumination patterns to suit a wide range of architectural site lighting.
- Highly efficient IP66 optics are protected from the elements and ensure optimal photometric performance.
- Innovative thermal management system to maximize LED performance and life, and to extend component life.
- Tremendous opportunities for additional energy savings through the use of controls and motion sensors.

# SFC/SFCR SlenderForm

## Canopy/Ceiling




- Elegant architectural design accompanies family aesthetic.
- Multiple lumen packages with output of up to 14,696 lm.
- Type 2, 3, 4, and 5 optics available.
- Aluminum heat sink fins built into top of luminaire.

### Ordering guide


Example: SFC-DD-5W-48L-700-NW-G2-UNV-MGY

| Luminaire              |  | Controls |                                     | Distribution    |                                  | LED Count            |  | Drive Current |                    |
|------------------------|--|----------|-------------------------------------|-----------------|----------------------------------|----------------------|--|---------------|--------------------|
|                        |  |          |                                     |                 |                                  | 48L                  |  |               |                    |
| SFC                    | SlenderForm Ceiling luminaire                                  | –        | Standard Luminaire                  | 3               | Type III                         | 48L 48 LEDs          |  | 250           | 250mA              |
|                        |  | DD       | 0-10V Dimming external leads        | 5W              | Type V, Wide Distribution        |                      |  | 400           | 400mA              |
| SFCR                   | SlenderForm Ceiling luminaire (recessed mounting) <sup>1</sup> |          | (controls by others) <sup>2,8</sup> | 5R              | Type V, Rectangular Distribution |                      |  | 550           | 550mA              |
|                        |  | MR       | Motion Response <sup>3,5,8</sup>    | CD              | Concentrated Downlight           |                      |  | 700           | 700mA              |
|                        |  |          |                                     |                 |                                  |                      |  | 900           | 900mA <sup>5</sup> |
| LED Color – Generation |  |          |                                     | Voltage         |                                  | Finish               |  | Options       |                    |
|                        |  |          |                                     |                 |                                  | MGY                  |  |               |                    |
| NW-G2                  | Neutral White 4000K, 70CRI Generation 2                        | 120      | 120V                                | MGY Medium Gray |                                  | F1                   | Single Fuse (120, 277, 347V) <sup>4,5</sup>            |               |                    |
| WW-G2                  | Warm White 3000K, 70CRI Generation 2                           | 208      | 208V                                |                 |                                  | F2                   | Double Fuse (208, 240, 277V) <sup>4,5</sup>            |               |                    |
| CW-G2                  | Cool White 5000K, 70CRI Generation 2                           | 240      | 240V                                |                 |                                  | F3                   | Double Fuse (208, 240, 480V) <sup>4,5</sup>            |               |                    |
|                        |  | 277      | 277V                                |                 |                                  | Canadian double pull |  |               |                    |
|                        |  | 347      | 347V                                |                 |                                  | DL                   | Diffusing Lens (reduces glare, see lumen values chart) |               |                    |
|                        |  | 480      | 480V                                |                 |                                  | PCB                  | Button Photocontrol <sup>3,4,5</sup>                   |               |                    |
|                        |  | UNV      | 120-277V                            |                 |                                  | BX                   | Bird Excluding Shroud <sup>5,6,7</sup>                 |               |                    |
|                        |  |          |                                     |                 |                                  | GL                   | Glass Lens assembly                                    |               |                    |

### SFC ceiling/canopy (surface ceiling mount)



### SFCR ceiling/canopy (recessed ceiling mount)



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.