

10 Round
Flutes

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Order guide

example: 306- 8 ABS B B D

Product Code	Pole Height	Finish	Outlet Location	Outlet Options	Tenon	Photoeye
306						
306	8' 10' 12' 14' 16'	ABS Antique Brass ACP Antique Copper ARD Antique Red ASI Antique Silver BLK Black BRN Brown BRZ Bronze FGN Forest Green GRA Granite IRN Ironstone RBZ Rustic Bronze SRT Shadow Rust VBZ Verde Bronze VCP Verde Copper VGN Verde VTC Vintage Copper WBZ Weathered Bronze WHT White	B 4" from Top of Base T 12" from Top of Pole	D Standard Duplex G GFI Duplex	N/A	B 120V C 208V - 277V

EPA values based on destructive break testing. For AASHTO ratings, contact factory.

Pole Data

Pole Model	Pole Shape	Pole Type	Shaft Dimension	Pole Fluted	Anchor Base Shape	Bolt Circle	Base Dim (in)
306	Round	Straight	4	Fluted	round	7	17 x 21.625

Pole Family	Catalog Number	Nominal Height (ft)	Tenon Section (in)	Wall Thickness (in)	EPA Rating 80 MPH (sq. ft)	EPA Rating 110 MPH (sq. ft)	EPA Rating 130 MPH (sq. ft)	Anchor Bolts (in)
306	306-8	8	3	0.125	19.69	9.94	8.47	3/4-15 bs
306	306-10	10	3	0.125	14.3	6.93	5.6	3/4-15 bs
306	306-12	12	3	0.125	10.69	4.96	3.68	3/4-15 bs
306	306-14	14	3	0.125	8.49	3.54	2.23	3/4-15 bs
306	306-16	16	3	0.125	6.86	2.42	1.07	3/4-15 bs

Specifications

CONSTRUCTION:

Cast aluminum anchor base. Cast aluminum removable access door. Round fluted post welded to base. Tenon secured to post top.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Signify Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

WARRANTY:


Please visit www.signify.com/warranties for more details on structural and finish warranty.

OUTLET:

GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

306 Poles and Brackets

Straight Round Fluted



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008