

Vaya Cove Color

Low profile cove lighting solution for dynamic color effects

Date: _____
Type: _____
Firm Name: _____
Project: _____

Vaya Cove is a reliable and cost-effective low profile linear LED luminaire for interior cove and accent lighting applications. Three lengths, standard 24V DC power and DMX-512 control make this product easy to use with Color Kinetics or third-party DMX controllers.

- Low Profile Housing - With just 22 mm (0.9 in) including the optional mounting clips, Cove LP offers one of the slimmest and most robust profiles for space-saving and yet reliable installations. The low profile allows for an inconspicuous light source that can be easily integrated or hidden in soffits or alcoves.
- Flexibility - Vaya Cove offers three different length options from 0.3 m (1 ft), 0.6 m (2 ft) up to 1.2 m (4 ft).
- Control - Compatible to ESTA standard DMX-512 control, Vaya Cove can be controlled by any Color Kinetics or third-party DMX controller or triggered from an overarching Dynalite system via iPlayer 3.



[Product page](#)

Beam Angle	110°
Lumens per foot*	38
Efficacy†	15
LED Channels	Red/Green/Blue

Input Voltage	24 VDC
Weight	90 g (0.2 lb) to 360 g (0.8 lb)
Housing Material	Extruded polycarbonate, white
Approbations	UL/cUL, FCC Class A, CE, CQC, RCM
Environment	Dry/Damp Location, IP20
Applications	Cove Lighting

Specification Sheets

* 305 mm (1 ft) lumen output measurements comply with IES LM-79-08 testing procedures. 610 mm (2 ft) and 1219 mm (4 ft) measurements are estimated based on the 305 mm (1 ft) measurements.

† Efficacy measurements are estimated based on the 305 mm (1 ft) measurements.

PDF Download	Beam Angle	Lumens*	Efficacy†	Power	Weight	Item Number	12 NC
RGB, 0.3 m (1 ft), CE/CQC/UL	110°	38	15	3.1 W	90 g (0.2 lb)	316-000004-00	910503702159
RGB, 0.6 m (2 ft), CE/CQC/UL	110°	75	15	6.2 W	180 g (0.4 lb)	316-000004-01	910503702160
RGB, 1.2 m (4 ft), CE/CQC/UL	110°	150	15	12.4 W	360 g (0.8 lb)	316-000004-02	910503702161

COLOR KINETICS vayaseries

© 2019 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics
www.colorkinetics.com/vaya