

KEENE

by  Signify

Wall mount

LytePro

LPW wall sconces



Designed for projects, built for stock

Providing high quality illumination, LytePro is available in 3 sizes with three optical distributions, multiple lumen packages, and is suitable for a range of mounting heights. Choose from select models ready to ship, or build the exact combination you need.

Features

- Three sizes to accommodate multiple mounting heights
- Lumen output ranges from 1,000 to 11,000 with efficacies up to 133 LPW
- Button photocell, motion response, battery pack, and field adjustable wattage options available with LPW32
- Types 2, 3, and 4 optical distributions available
- 3000K and 4000K color temperatures available
- All models are DLC qualified
- 5 year limited warranty

Benefits

- Low-profile design to complement and blend in with surroundings
- Provides energy saving replacement for incandescent, compact fluorescent and HID lamp sources up to 320W
- Optical distributions offer full cutoff performance and excellent uniformity for precise wall and area illumination
- Easily mounts to a variety of junction box types or fastens directly to wall for seamless retrofitting
- Outstanding long life provides maintenance savings



Dependable quality for peace of mind

LytePro is a trustworthy and proven winner with a history of quality and is now available with even more configurations. This wall scone family combines excellent performance, design, and value to meet both stock and project needs.



LPW7



LPW16



LPW32



Button photocontrol
(PCB)



Motion response
(IMRI3)



Universal mounting plate accessory
(LPWCVRPLT-BZ)

Product comparison



	LPW7	LPW16	LPW32
Distribution	Type 2	Type 2, 3, or 4	Type 2, 3, or 4
Lumen output range (4000K)	1,050	2,700/4,000/5,500	6,000/8,500/11,000
Average system watts	10	22/34/48	45/65/90
Efficacy	108	102-122	108-133
HID replacement ¹	50W	70W/100W/150W/175W	175W/250W/320W
Color temperature	3000K, 4000K	3000K, 4000K	3000K, 4000K
Recommended mounting height range	7'-10'	10-15'	15-25'
BUG rating	B1-U0-G0	B1-U0-G1	B1-U0-G2 (65W) or B2-U0-G2 (90W)
Ambient temp. rating	-40°C to 40°C (-40°F to 104°F)	-40°C to 40°C (-40°F to 104°F)	-40° to 40°C (-40° to 104°F)
Approx. luminaire weight	4 lbs (1.8Kg)	6 lbs (2.7Kg)	9 lbs (4Kg) or 11 lbs (5Kg) with EBP
IP-Rating	IP65	IP65	IP65
DLC Qualified (standard)	✓	✓	✓
Emergency Battery Backup (0° to 40°C)	✗	✗	✓
Field Adjustable Wattage Selector (FAWS)	✗	✗	✓
Motion response	✗	✗	✓
Photocontrol button	✓	✓	✓


¹ Based on comparisons of design mean lumens of metal halide lamps in typical wall mount HID luminaires.

Designed to meet any application needs

Optical distributions

LPW7

Based on LPW7-10-NW-G3-2 at 10' mounting height




LPW7 10' mounting height

Mounting height	6 ft	8 ft	10 ft
Multiplier	1.23	1.14	1.00


LPW16

Based on LPW16-30-NW-G3 at 15' mounting height




LPW16 15' mounting height

Mounting height	10 ft	12 ft	15 ft
Multiplier	1.29	1.14	1.00



LPW16 15' mounting height

Mounting height	10 ft	12 ft	15 ft
Multiplier	1.57	1.34	1.00




LPW16 15' mounting height

Mounting height	10 ft	12 ft	15 ft
Multiplier	1.46	1.27	0.87


LPW32

Based on LPW32-70-NW-G3 at 20' mounting height




LPW32 20' mounting height

Mounting height	18 ft	20 ft	23 ft
Multiplier	1.05	1.00	0.93



LPW32 20' mounting height


Mounting height	18 ft	20 ft	23 ft
Multiplier	1.14	1.00	0.79



LPW32 20' mounting height

Mounting height	18 ft	20 ft	23 ft
Multiplier	1.16	1.00	0.76

Mounting height guide



LytePro ordering information

For a complete list of configurations and ordering information, download the spec sheets at keene-lighting.com.
Our select list of stocked luminaires is shown below.

Stocked luminaires

Catalog Number	Description	Master Pack, Qty	UPC Code
LPW7			
LPW7-G3-8-BZ	LPW7, 10W, 4000K, Type 2, 120-277V, Bronze textured paint	6	622252813858
LPW7-G3-8-DGY	LPW7, 10W, 4000K, Type 2, 120-277V, Dark gray textured paint	6	622252813841
LPW16			
LPW16-G3-8-BZ	LPW16, 30W, 4000K, Type 3, 120-277V, Bronze textured paint	6	622252813872
LPW16-G3-8-DGY	LPW16, 30W, 4000K, Type 3, 120-277V, Dark gray textured paint	6	622252813865
LPW32			
LPW32-G3-8-BZ	LPW32, 70W, 4000K, Type 3, 120-277V, Bronze textured paint	3	622252813896
LPW32-G3-8-DGY	LPW32, 70W, 4000K, Type 3, 120-277V, Dark gray textured paint	3	622252813889

Stocked accessories (must be ordered separately)

Catalog Number	Description	Master Pack, Qty	UPC Code
LPWCVRPLT-BZ ²	LPW Universal wall cover mounting plate, Bronze textured paint	(none)	786034960618

² Other colors available upon request as made-to-order



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.