

Multiple styles for your application

Gardco LED 100 line wall sconces provide compact designs that provide wide flexibility in high performance illumination. The broad choice in housing styles and optics offers numerous options in balancing the illumination and aesthetic requirements of a project. Whether they are used on building entrances, over ATMs or on loading docks, there is no need to compromise appearance for performance. Available with 4 different low-profile forms to choose from, 100 line has you covered.

Benefits

- Multiple lumen packages with output ranging from 1,358lm to 12,045lm.
- Energy saving LEDs provide up to 136 LPW efficacy.
- $\boldsymbol{\cdot}$ Three distribution patterns available in Type 2, 3, 4.

- Emergency Battery Back Up available to provide path-of-egress illumination.
- Energy saving control options, such as motion response and Dynadimmer.

100 LED Wall Sconce

Luminaires that offer new opportunities to make a sustainable architectural statement and provide a much-needed alternative to glare-inducing wall packs. Used for illuminating building façades, loading docks and walkways.



101L Trapezoidal Wedge



102L Rounded Wedge



104L Half Cylinder



106L Quarter Sphere

Finish

Five standard finish options available in black, white, dark grey, and medium grey. Optional and special finishes also available.

Die cast housing

Rugged, die-cast aluminum housing for maximum durability.



Integral controls

Optional Emergency Battery Backup and Programmable Motion Response are integral to the luminaire, and do not require any external components.

Optical Distributions


Type 2, 3, and 4 distributions available

IP66 Rated

IP66-rated optics.

Mounted fixtures

- 1. 101L-16L-530-NW-G2
- 2. 101L-16L-700-NW-G2 3. 101L-16L-1000-NW-G2
- 4. 101L-32L-530-NW-G2
- 5. 101L-16L-1200-NW-G2
- 6. 101L-32L-700-NW-G2
- 7. 101L-32L-1000-NW-G2





© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify

Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners