Downlighting

LIGHTOLIER

by (signify

LyteProfile LED

SL Shower Light Trim



Experience the change, see the difference... again, and again

Architectural non-conductive trim provides the right illumination and added safety you need.

Benefits

UniFrame's non-conductive shower light trim is not just a modification to the downlight product, it was purposefully designed with wet locations in mind. The non-conductive flush mount lens with pre-installed gasket takes the worry out of wet location safety. It also reflects the lustrous architectural look and lighting performance that you've come to expect in all of Lightolier's newest LED downlights.



SL LyteProfile LED Shower light trim downlighting

Features

Apertures: 3", 4", & 6" round Finish: Matte white flange with diffuse lens

Lumens: 3" in 500-1500lm; 4" in 500-2500lm; 6" in 1000 to 3000lm

Construction: Flush mount Non-conductive lens with pre-installed gasket

Installation: One-piece reflector and lens allows for similar installation as standard trims*

Labels: cULus wet location

Warranty: 5 year



Frame (frame + engine/trim = complete product)

example: 6RNLC

Series	Aperture	Installation	Options			
 3 LyteProfile LED 3" 4 LyteProfile LED 4" 6 LyteProfile LED 6" 	R Round	N New construction (Non-IC)	 Universal 120/277V (specify for POE) LC Chicago Plenum EM Emergency¹ 	3 3radio Radio	347V (not compatible with ELV dimming) 347V Integral Interact Pro RF sensor (enables wireless connected lighting control) Integral Interact Pro RF sensor (enables wireless connected lighting control)	
		R Remodeler (Non-IC) ¹	 Universal 120/277V (specify for POE) 	3 347V (not compatible with ELV dimming)		
		A AirSeal (IC) ²	 Universal 120/277V (specify for POE) 			

Engine/Trim

example: P6RSI 20835CD710U

Series	Style	Lumen	CRI/CCT ⁶	Reflector (white flange)	Dimming ⁷	Voltage
P3R LyteProfile LED 3" Round ⁴ P4R LyteProfile LED 4"	SL Shower light	 10 1000 lm 15 1500 lm⁴ 20 2000 lm 25 2500 lm⁵ 30 3000 lm 	827 80 CRI / 2700 K 830 80 CRI / 3000 K 835 80 CRI /	WH White (matte)	Z10 0-10V 1% L Lutron LDE1 EcoSystem (fade-to-black)	U Universal (120/277/347V)
Round⁵ P6R LyteProfile LED 6" Round		35 3500 lm	3500 K 3500 K 840 80 CRI / 4000 K 850 80 CRI / 5000 K		P Power over Ethernet (PoE) Only compatible with 100	E Ethernet 48V DC Olm to 2500lm options

1. Remodeler available only for 4-inch and 6-inch apertures

2. Emergency (EM) frame includes emergency battery with ceiling and reflector mountable test switch (see spec sheets for details and limitations). Integral emergency battery not compatible with Power over Ethernet configurations.

3. Interact Pro (RADIO & 3RADIO) requires above ceiling access.

Refer to spec sheets for all dimming options.

4. P3R 3-inch available up to 1500lm

5. P4R 4-inch available up to 2500lm

6. See spec sheets for 90CRI options. 7. Consult factory for available Dali and 0-10V dimming to 0.1% availability.



* Wet location rated shower light is

applicable in any installation requiring

non-corrosive applications, or where a

diffused lens at the ceiling is required.

limited warranty.

dead front trims, interior or exterior

Visit Signify.com/warranties for more information on Signify's standard 5-year

Note: For reflector mounted test switch add "EM" to end of catalog code (example: P6RDL20835CDZ10UEM). Leave blank for ceiling mounted test switch. Reflector mounted test switch requires above ceiling access and 1.25" max ceiling thickness for downlight only. See LED-EM spec sheet for more details.

signify

herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify Canada Ltd. 281 Hillmount Road,