LIGHTOLIER

by (s)ignify

Sleek and Seamless

B

Đ

Alcyon LED

I

3

Vertical Track Heads & Recessed Multiples with AccuRender technology



E

Ð

Alcyon

Track Heads & Recessed Multiples

Lightolier is a global market leader widely recognized for its innovative LED lighting solutions with an unmatched commitment to technology leadership, reliability, visual appeal and high performance. Track and recessed multiple cylinder utilize the same LED and optical architecture. They are designed to meet the most demanding accent lighting applications allowing for lighting and aesthetic consistency within any space.



AccuRender Technology (CRI 90+)

The right light brings colors to life. Our new AccuRender technology helps ensure colors are rendered more accurately and consistently, while doing so as efficiently as CRI 80 products.



Standard CRI 80 Good color rendering and high efficacy



Standard CRI 90 Better color rendering and low efficacy

AccuRender Best color rendering, color preference and high efficacy

Enjoy design flexibility

- Full range of products and options:
- Available soon in across Lightolier portfolio for application flexibility
- Multiple color temperatures (CCTs) and lumen packages offered

Promote savings

High efficacy, with no penalty:

- Energy efficacy compares well to conventional 80 CRI
- Up to 25% more energy savings vs competitor 90 CRI¹
- Helps meet Title 24 requirements

Show your true colors

High color rendering:

- True to life colors to help energize your environment and render better flesh tones critical for healthcare hospitality and retail applications.
- $\begin{array}{ll} R_{s} \text{ up to 94 CRI} & \cdot & R_{f} \text{ up to 92 TM-30} \\ R_{9} \text{ up to 67 CRI} & & R_{f,h1} \text{ up to 91 TM-30} \\ G_{a} \text{ up to 99 CRI} & & R_{9} \text{ up to 100 TM-30} \\ C_{9} \text{ up to 94 CRI} & & R_{cs,h1} \text{ up to -5\% TM-30} \end{array}$

Achieve color balance

Best in class color consistency:

 Promote aesthetic harmony in your space with ≤ 2 SDCM

Crisp White

Dial-up the drama of your display. Highlight the variances in white tones, add contrast to blacks and create a real pleasing sparkle effect while retaining warm skin tones.

Premium White

The new benchmark for retail fashion. Delivering stronger and brighter whites via the best lighting technology on the market with minimal compromise to energy savings.


Premium Color

Enhance the contrast between colors and whites to achieve new depths of color rendering for a vibrant saturated fashionforward visual experience that won't affect the atmosphere and will have a positive effect on energy efficiency.

Standard Color

Standard CRI 90

LED Color Recipes (90CRI/3000K)





Discrete. Versatile. Visually Comfortable.

Alcyon combines compact with power to keep attention focused exactly on designated areas of interest. Now available with AccuRender 90+ CRI technology for the highest color quality at the highest efficacy. Ideal for display, accent and task lighting and offer higher efficiency than incandescent or halogen sources leading to energy savings with no ultraviolet or infrared radiation. Alcyon provides concentrated light which dramatically draws interest to objects and elements in a space.

Benefits

- Perfect the lighting in your spaces with CrispWhite, PremiumWhite, or Premium Color
- 1000 lm 10° Narrow Spot delivers more than 24,000 CBCP for excellent punch
- Light quality consistency, specifically designed for retailers
- Integrated "invisible" heat sink, designed with a passive cooling methodology

LLAV Alcyon LED Vertical

Track Heads (1000lm, 1400lm, 2000lm & 3000lm)

Features

- Efficacy: up to 121 lm/w
- Lumens: 1000 2000 lm
- Watts: 9 34 W
- CRI: 90+
- CCT: 2700 4000 K
- Volts: 120/277V (50/60Hz)
- Lifetime: 90,000 hrs (L70)



Fixture

example: LLAV01930LWH

Accessories² (order separately) example: LLA11SNBK

Series		Lumens	CRI/CCT	Adapters	Finishes		
LLAV	Alcyon Vertical Track Heads	01 1000 lm 11 1400 lm 20 2000 lm 30 3000 lm	927 90CRI / 2700K 930 90CRI / 3000K 935 90CRI / 3500K 940 90CRI / 4000K LED Color Recipes CW30 CW30 90CRI / 3000K Crisp White PW30 PW30 90CRI / 3000K Premium White PC30 PC30 90CRI / 3000K Premium Color Premium Color	L Lightolier H Halo J Juno P Prospec ¹	AL Aluminum BK Matte Black WH Matte White		

Series			Finishes		
Accessory LLAV11AH LLAV12AH	Alcyon Small	AL	Aluminum Matte White		
LLAVIZAN	Alcyon Medium	BK	Matte Black		
Snoots					
LLA11SN	Alcyon Small	AL	Aluminum		
23SNT6	Alcyon Medium	WH	Matte White		
		BK	Matte Black		
Diffusion fi	Ims				
LLAV11	Alcyon Small	SF	Soft Focus		
LLAV12	Alcyon Medium	FR	Frosted Etched		
		LS	Linear Spread		
		SY	Symmetrical Spread		

Reflector

Series	Lumens	Beam spreads (order separately)			
LLAV Alcyon Reflectors	11 Small (for 1000, 1400, & 2000lm) 12 Medium (for 3000lm)	RNS10° Narrow SpotRS18° SpotRNF24° Narrow FloodRF36° Flood			

1. Prospec is only offered in WH & BK finishes.

2. Aperture ring on the fixture can hold a maximum of 1 film and 1 snoot.

3. Accessory holder can hold a maximum of 1 hex cell, 1 film, and 1 snoot.

4. Hex cell needs to be ordered with an Accessory holder.

example: LLAV11RNS

 LLAHCA11
 Alcyon Small (matte black only)

 AL4HC
 Alcyon Medium (matte black only)

 A full range of high performance accessories for tinting, coloring

A full range of high performance accessories for tinting, coloring and shaping of the light beam. All accessories are designed to attach easily. A complete accessory consists of a size and series suffix.

Assembly Small

(1000lm, 1400lm & 2000lm)



Assembly Medium (3000lm)



cULus Listed. 5 year warranty. Suitable for damp location ENERGY STAR® certified (excluding Crisp White, Premium White, and Premium Color configurations). Accessories are not ENERGY STAR° qualified.





Clean architectural **design**

Alcyon combines compact with power to keep attention focused exactly on designated areas of interest. Now available with AccuRender 90+ CRI technology for the highest color quality at the highest efficacy. Offer high-performing, target illumination to meet today's accent lighting needs in retail environments. Alcyon recessed lighting utilizes the same LED technology and reflectors as the Alcyon vertical track heads, providing performance consistency and design continuity within a space.

Benefits

- Perfect the lighting in your spaces with CrispWhite, PremiumWhite, or Premium Color
- · Market leading efficiency and "candlepower punch"
- Tool-less aiming, tilt and pull-down design

LLAVRM Alcyon LED Vertical

Recessed Multiples (1000lm, 1400lm & 2000lm)

Features

- Efficacy: up to 120 lm/w
- Lumens: 1000 2000 lm
- Watts: 10 21W
- CRI: 90+
- CCT: 2700 4000 K
- Volts: 120/277V (50/60Hz)
- Lifetime: 120,000 hrs (L80)



Accessories¹ (order separately)

example: LLA11SNBK

Frame example: LLAVRM11H2120						
Series	Lumens	Heads	Voltage			
LLAVRM Alcyon Vertical Recessed Multiples	11 1000,14001m 20 20001m	 H1 1 head H2 2 head H3 3 head H4 4 head 	120 120V 277 277V			

Series		Finis	Finishes			
Accessory	holders ²					
LLAV11AH	Alcyon Small holder	WH	Matte White			
LLAV12AH	Alcyon Medium holder	вк	Matte Black			
Snoots						
LLA11SN	Alcyon Small snoot	WH	Matte White			
23SNT6	Alcyon Medium snoot	вк	Matte Black			
Diffusion fi	Ims					
LLAV11	Alcyon Small film	SF	Soft Focus			
LLAV12	Alcyon Medium film	FR	Frosted Etched			
		LS	Linear Spread			
		SY	Symmetrical Spread			


Hex cell louvers³

LLAHCA11 Alcyon Small louver (matte black only) AL4HC Alcyon Medium louver (matte black only)

A full range of high performance accessories for tinting, coloring and shaping of the light beam. All accessories are designed to attach easily. A complete accessory consists of a size and series suffix.

Assembly Small (1000lm & 1400lm)







Fixture with white flanges

example: LLAVRMWH1130H2

example: LLAV11RNS

Series		Finis	h	Lun	nens	CRI/0	сст	Hea	ds
LLAVRM	Alcyon Vertical Recessed Multiples		White Black	01 11 20	1000 lm 1400 lm 2000 lm	935 940 LED	Premium White	НЗ	1 head 2 head 3 head 4 head

Reflector

Series	Lumens	Beam spreads (order separately)
LLAV Alcyon Reflectors	11 Small (for 1000, 1400lm) 12 Medium (for 2000lm)	RNS 10° Narrow Spot RS 18° Spot RNF 24° Narrow Flood RF 36° Flood

1. Aperture ring on the fixture can hold a maximum of 1 film and 1 snoot.

2. Accessory holder can hold a maximum of 1 hex cell, 1 film, and 1 snoot.

3. Hex cell needs to be ordered with an Accessory holder.

cULus Listed. 5 year warranty Suitable for damp location ENERGY STAR® certified (excluding Crisp White, Premium White, and Premium Color configurations). Accessories are not ENERGY STAR^o qualified.

Consistent design attributes

Take track accent lighting design from subtle to bold

For new construction or retrofit installations offering the most competitive adapters available.*

High impact applications with up to 30,000 candela at 80 CRI / 3000K performance. Multiple CRI and CCT options for excellent color rendering.

Industry leading low profile form-factor at less than 1-inch between the track head and the ceiling.



Small (1000lm, 1400lm & 2000lm)



Medium (3000lm)



Three-part system

Taking accent lighting to the next level

Designed to offer high-performing, target illumination to meet today's accent lighting needs. This recessed lighting utilizes the same LED technology and reflectors as the track heads, providing performance consistency and design continuity within a space.

Recessed multiples utilize the same LED and optical architecture as the track heads. They are also designed to meet the most demanding accent lighting applications: allowing for lighting and aesthetic consistency within any space.



1. Pull-down extension

Offers additional aiming control by extending the fixture below the rectangular aperture. Allows users to choose a clutter-free look or target a beam of light on merchandise or display areas for optimal efficiency.

2. Tool-less aiming

Pivot mounts offer tool-less aiming with 360° of horizontal rotation and 180° of vertical tilt for maximum aiming control.

3. Multi-head system

Fixtures are available as $3\frac{1}{2}$ " (600 lm and 1000 lm) or $5\frac{1}{6}$ " (2000 lm) aperture cylinders and can be configured as a one-, two-, three- or four-head installation.



Avaiable in both small 3.5" dia. (left) and medium 5.125" dia. (above) sizes.

Sleek and Seamless

Specifically designed to bring attention to designated areas of interest



Discrete in any space, allowing for the emphasis on key points of interest within commercial and retail spaces without sacrificing impact or efficiency. Alcyon provides a wide range of personalization options, easy installation and compatibility with existing track rails so it's never been easier to create a unique experience that distinctly sets you apart from others.





Finishes are available in Aluminum, Matte White and Matte Black satin painted finishes.

Dimensions (1000lm, 1400lm & 2000lm)












Dimensions (3000lm)




















(s)ignify

© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.