

1 2 3 4 5 6 7 8 9 10

A

B

C





D

E

F

G

H



I out	Pin 1	Pin 2
0.2A	ON	ON
0.25A	ON	OFF
0.3A	OFF	ON
0.35A	OFF	OFF

Specification item	Value	Unit
Length (A1)	210.0 (+/- 0.3)	mm
Mounting hole distance (A2)	198.5 (+/-0.3)	mm
Width (B)	30.0 (+/-0.5)	mm
Height (C)	21.0 (+/-0.5)	mm
Mounting hole diameter (D1)	4.1 (+/-0.2)	mm
Mounting hole diameter (D2)	4.1 (+/-0.2)	mm

GB/T 1804-2000m (Unit: mm)										
SIZE RANGE	0.5-3	>3-6	>6-30	>30-120	>120-400	>400-1000				
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8	ITEM	ASSEMBLY NO.	QUANT.	
GENERAL ROUGHNESS ✓	UNIT mm	MATERIAL					MODEL NAME			
							CertaDrive EL Version			
SCALE	PROJECT TYPE 	TREATMENT					ORDER NO.	QUANT.		
		TITLE: Xi 65W 200-350mA 185V DS 230V AW					PART NUMBER: 9290 039 53601		2025-02-28 A	
REV	CHANGE NO.	DATE								
DESIGNED BY		Crane Cui		CHECKED BY		1	SH.	SH. 110 of 1	FORM NO.	A3
DRAWN BY				APPROVED BY		REVISED BY		Signify (China) Investment CO., LTD		



1 2 3 4 5 6 7 8 9 10