

Stonco

by  Signify

Special Purpose

Roughlyte

Surface and ceiling mount,
incandescent



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Stonco Roughlyte is available in wattages ranging from 100 to 200. Applications include wall, columns, ceilings and canopies in exterior applications. Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only). Features include heat and shock resistant glass or polycarbonate globe and cast aluminum bayonet guard with Allen head security screws. Not recommended for hazardous locations.

Ordering guide

Example: VK1GC

Series	Wattage	Lens
<input type="text" value="VK"/>		
VK Surface and ceiling mount	1 100W 2 200W	GC Glass globe and cast guard

Product Specifications

- All incandescent Roughlyte ceiling and canopy fixtures are not supplied with a lamp. This fixture requires a medium base incandescent A lamp. The lamp can be clear or coated.
- Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only).
- cULus listed for wet locations.
- **Not recommended for use in hazardous locations.**


VK Roughlyte surface and ceiling mount

VK

- 100W fixtures fit all 3-1/2" round and octagon boxes and all 4" round boxes.
- Heat and shock resistant glass globe.
- Sockets are pre-wired with extra long 1/2" stripped leads.
- For 3/4" conduit, use VK series with VXL13 universal box.

Dimensions

Catalog No.	Height (H)	Dia. (D)
VK1GC	7-1/2"	4-1/4"
VK2GC	9-1/4"	5-1/4"



Accessories



4" Round boxes

Die-cast aluminum for use with conduit, Stonco ceiling, surface and wall fixtures and flood lights. Four side and one back hole tapped 3/4" as shown. Heavy-duty gasket, screws, four aluminum five-threaded plugs. No cover.

Catalog No.	Tap size	Description
VXL13	3/4"	Mounting box



V131
Cast Aluminum Guard

Guards

Cast aluminum guards are twist on/off bayonet type, includes allen head security screws. Shipped with threaded ring adapter for use with standard threaded bases or the new RoughLyte bases.

Catalog No.	Cast guard Fits globe diameter
V131	3-1/2"



VGC100
Clear Glass Globe



VGP100
Clear Prismatic Globe

Colored and specialty globes

Full molded threads. Fit all Stonco housings. Globes for vertical mounting only.

Catalog No.	Description	Catalog No.	Description
3-1/2" Globe dia. Height - 6 11/16"		4-3/8" Globe dia. Height - 8 3/8"	
VGC100	Clear*	VGC200	Clear*
VGP100	Clear, prismatic		
VGA100	Amber (60W max.)		
VGB100	Blue (60W max.)		
VGR100	Ruby (60W max.)		
3-1/2" Globe dia. LEXAN		4-3/8" Globe dia. LEXAN	
VPRC5	Clear, prismatic (60W Max.)	VPRC10	Clear, prismatic (75W Max.)

*Standard with all incandescent glass fixtures.

NOTE: Use of colored globes will down-rate wattage.



VGR100
Ruby Glass Globe



VPRC10
Prismatic Lexan Globe

