



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Ordering Guide

Example: TC152-12

Product Code	TC152-12	Transformer
--------------	----------	-------------

Specifications

HOUSING:

Housing and cover are polyester powdercoated steel with removable door. Two (2) 1/2" conduit knockouts on each side. Internal transformer is epoxy encapsulated. Exterior Mounting - Transformer should be mounted on the wall, structure, or post in the vertical position. Cable entries should be positioned downward.

ELECTRICAL ASSEMBLY:

6-ft heavy-duty 18-3 AWG, 105° C, SJT power cord with 3 prong grounded wall plug. The transformer is thermally protected and is shielded between the 120V input and the low voltage output, for safety. Insulation type transformers for safe operation. Euro-Board terminal block for easy low voltage cable attachment. Line voltage amperage draw: 150VA = .9AMP. 50/60Hz input. Consult factory for details.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

WARRANTY:

Ten-year limited warranty.

Height :

7" (178mm)

Width:

3 1/2" (89mm)

Depth:

3 1/2" (89mm)

