

4" x 3"  
Tapered

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

## Order guide

example: P1150 86 A T D

Product Code	Pole Height	Finish	Outlet Location	Outlet Options
<b>P1150</b>				
P1150	86" (8' 6") 106" (10' 6") 126" (12' 6")	A Black B White G Verde H Bronze I Gray J Green	T 12" Down from Top - Aligned with House Side B 4" Up from Top of Base - Aligned with House Side	D Standard Duplex G GFI Duplex

Note: Top outlets not available with the HFP arms. EPA values based on destructive break testing. For AASHTO ratings, contact factory.

## Pole Data

Pole Model	Pole Shape	Pole Type	Shaft Dimension	Pole Fluted	Anchor Base Shape	Bolt Circle	Base Dim (in)	Hand Hole Dim (in)
P1150	Round	Tapered	4 to 3	Smooth	round	7	11 x 30	4.25 x 4.5

Pole Family	Catalog Number	Nominal Height (ft)	Tenon Section (in)	Wall Thickness (in)	EPA Rating 80 MPH (sq. ft)	EPA Rating 100 MPH (sq. ft)	Anchor Bolts (in)
P1150	P1150-8.5	8.5	3	0.125	9.06	5.42	1/2-15 bs
P1150	P1150-10.5	10.5	3	0.125	7.06	4.03	1/2-15 bs
P1150	P1150-12.5	12.5	3	0.125	5.55	2.95	1/2-15 bs

## Specifications

### HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy . 6063-T6 Extruded aluminum. Anchor rods are hot dipped galvanized steel.

### FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

### WARRANTY:


Please visit [www.signify.com/warranties](http://www.signify.com/warranties) for more details on structural and finish warranty.

### OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

# P1150 Poles and Brackets

## Tapered Round Smooth



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

