

### Landscape

Step light

RSS2/RSC2/RSV2



Hadco LED step light line-voltage landscape luminaire has interchangeable LED color temperature between 3K and 4K CCT. This adjustable luminaire also has the ability to switch between 5 preset light outputs.

Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

#### **Ordering guide**

Ordering guide example: RSC2-AK5DG2					
Series		Finish	Optics	Source	Generation
RSC2	Aluminum step light	A Black H Bronze	К5	<b>D</b> LED	G2 Generation 2
RSS2	Polycarbonate Step light	A Black	К5	D LED	G2 Generation 2
RSV2	Vertical aluminum step light	A Black H Bronze	К5	<b>D</b> LED	G2 Generation 2

#### Optional for early installation

Series	Finish	Option	
RS2			
RS2	A Black H Bronze	HO Housing only (pre-shipment)	

Use when Housing Only (HO) is ordered for pre-shipment to complete catalog number of fixture without housing.

#### Accessories

Construction mounting kits				
МАКМ	Masonry kit			
MAKNS	New Stud Wall kit			
MAKES	Existing Stud Wall kit			

All units supplied with mounting hardware for concrete pour installation. If other mounting kits are required, order accessory.





## RSS2/RSC2/RSV2 Step light


#### **Dimensions and finishes**

#### RSC2

Aluminum step light









9"

RSS2 Polycarbonate step light



#### Bottom view of all



### RSS2/RSC2/RSV2 Step light

#### Specifications

#### Housing

Die-cast aluminum back box contains less than 0.3% copper to prevent corrosion in concrete or masonry applications.

#### Trim ring

Die-cast aluminum trim contains less than 0.3% copper to resist corrosion.

#### Reflector

Specular aluminum formed reflector.

#### Faceplates

Cast louver

Die-cast copper-free aluminum with  $45^{\rm o}$  cutoff, with frosted tempered glass.

#### **Opal lens**

Opal UV stabilized injection molded polycarbonate with frosted glass siliconed on inside for durability.

#### Louvers

Clear UV stabilized injection molded polycarbonate with  $45^{\circ}$  louvered screen insert.

#### Finish

#### Polycarbonate

Color impregnated composite material in; black or bronze (RSS2).

Aluminum parts have zinc-rich primer and for durability a thermoset powder coat in; black or bronze (RSC2 /RSV2).

#### LED

Delivers 70% lumen maintenance at 50,000 hours.

Color temp (CCT): Warm white (3000K) is standard. Cool white (4000K) is optional and is switchable at the fixture.

#### Controls

Class 2 driver with AOC and 0-10V dimming. Design allows easy-access to integral switch with 5 preset light outputs, see lumen matrix. Remove lens cap with [2] screws and simply adjust the slider switch by hand.

#### ADA compliant

Compliant when used in indoor and outdoor wall applications.

#### Electrical

9.2W (on high setting) Input voltage range (VAC): 120-277V. Pre-wired with #18 AWG black, white and ground wire for ease of connection. Also has #18 AWG grey and violet for 0-10V Analog Class 2 dimming, capped off to help prevent cross wiring with line- voltage wires.

#### Labels

ETL and cETL listed.

#### Warranty

5 year limited warranty.

#### Lumen Matrix

Switch Settings (Nominal)	Typical Wattage Consumption	RSC2 Warm	RSC2 Cool	RSS2 Warm	RSS2 Cool	RSV2 Warm	RSV2 Cool
100% (5)	9.2	179	175	427	435	153	156
80% (4)	8.0	158	154	376	383	135	137
60% (3)	6.2	122	119	290	296	104	106
40% (2)	4.4	85	83	203	206	73	74
20% (1)	2.7	46	45	110	112	39	40

# Signify

© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone: 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owner