

Vaya Linear MP RGB

Powerful exterior line-voltage linear grazing luminaire with dynamic color-changing lighting effects

Date: _____
Type: _____
Firm Name: _____
Project: _____

Vaya Linear MP is a reliable and cost-effective LED wall grazing luminaire for both interior and exterior use that minimizes initial investment, while offering exceptional flexibility to create eye-catching wall washing and wall grazing effects. A wide range of color and CCT options, in either static on/off or with dynamic color control, adjustable mounting brackets, wide or elliptical beam angles offer a comprehensive toolbox for your facade lighting needs. The discreet design with integrated power supply makes wiring simple, fast and reliable.

- Powerful - Throwing light with 10lx up to 30 m / 1fc up to 98 ft (elliptical beam), the Linear MP is ideal for grazing of mid-sized walls and facades.
- Simple - Directly processes 100 to 277 VAC input, all in one slim housing, eliminating the need for bulky external low voltage power supplies and related cabling limitations, allowing for greater installation flexibility and a lean installation.



[Product page](#)

Beam Angle	10° x 50°, 50°
Lumens per foot*	477 to 484
Efficacy for 50°	35.1
Efficacy for 10°x50°	36.4
LED Channels	Red/Green/Blue

Input Voltage	100 to 277 VAC, 50/60 Hz
Weight	1.3 kg (2.9 lb) for 1 ft 3.6 kg (7.9 lb) for 4 ft
Housing Material	Extruded aluminium, dark grey anodized finish
Approbations	UL/cUL, FCC Class A, CE, PSE, RCM
Environment	Dry/Damp/Wet Location, IP66
Applications	Wall Grazing

Specification Sheets

PDF Download	Beam Angle	Lumens*	Power	Weight	Item Number	12 NC
RGB, 50°, 0.3 m (1 ft), CE	50°	477	18 W	1.3 kg (2.9 lb)	316-000011-00	912400130056
RGB, 50°, 0.3 m (1 ft), UL	50°	477	18 W	1.3 kg (2.9 lb)	316-000011-04	912400130060
RGB, 50°, 1.2 m (4 ft), CE	50°	1,906	60 W	3.6 kg (7.9 lb)	316-000011-02	912400130058
RGB, 50°, 1.2 m (4 ft), UL	50°	1,906	60 W	3.6 kg (7.9 lb)	316-000011-06	912400130062

COLORKINETICS
vaya series

Specification Sheets (cont.)

PDF Download	Beam Angle	Lumens*	Power	Weight	Item Number	12 NC
RGB, 10° x 50°, 0.3 m (1 ft), CE	10° x 50°	484	18 W	1.3 kg (2.9 lb)	316-000011-01	912400130057
RGB, 10° x 50°, 0.3 m (1 ft), UL	10° x 50°	484	18 W	1.3 kg (2.9 lb)	316-000011-05	912400130061
RGB, 10° x 50°, 1.2 m (4 ft), CE	10° x 50°	1,934	60 W	3.6 kg (7.9 lb)	316-000011-03	912400130059
RGB, 10° x 50°, 1.2 m (4 ft), UL	10° x 50°	1,934	60 W	3.6 kg (7.9 lb)	316-000011-07	912400130063

* Lumen output measurements comply with IES LM-79-08 testing procedures.

COLORKINETICS vayaseries

© 2019 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics
www.colorkinetics.com/vaya