

# A hard-working, die-cast utility light that is built to last

- **Enhanced performance**  
Quality and reliability to improve sense of security
- **Flexible use**  
Multiple lumen packages and optic options
- **Built to last**  
Die-cast aluminum housing and optional aluminum arm and bracket
- **Reduced Light Pollution**  
Dark Sky compliant configurations available
- **Designed to save you money**  
Outstanding efficacy translates to energy savings
- **Controls Ready**  
Features a 7-pin receptacle with dimming driver



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

All trademarks are owned by Signify Holding or their respective owners.

PLu-2205PM 04/23

[www.lumec.com](http://www.lumec.com)

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

# LUMEC

by @signify

Roadway

RoadFocus Plus

RPRS Security Light



## Your heavy duty lighting solution

# RoadFocus Plus


# A reliable and affordable solution

## RPRS Security Light



### A utility light that is built to last

RoadFocus Plus LED Security Light is a reliable and affordable solution for rural roads and trails, farm yards, industrial parks and countless other general lighting applications. RoadFocus Plus LED Security Light provides dependable, high quality lighting that is IP66 rated and easy to install as well as maintain.



### Ideal for a wide variety of locations

These areas require dependable, high quality lighting that is IP66 rated and easy to install as well as maintain.

- Pole mounted security
- Residential or Rural streets
- Industrial park/warehouses
- Rural access drives/pathways
- Parking lots
- Farm yards
- Boat docks/marinas
- Public trails

### Key benefits include

- Reliable/Built to last
- Low Maintenance
- Affordable
- Heavy Duty
- Enhanced performance
- Worry-Free Operation
- Outstanding Energy Efficiency
- Dark Sky Rated Configurations\*

\* IDA approved if ordered with 3000K CCT and without refractor.

### Components

1. **Quick release & tool-less entry**
2. **Surge protection:**  
Optional SP1 and SP2 surge suppressors protect the luminaire.
3. **Twist lock receptacle:**  
Tool-less 7-pin NEMA twist lock receptacle facilitates connected lighting solutions that can quickly and easily be upgraded in the future. (shown with optional photocell)
4. **Bird guard:**  
Standard with all RoadFocus luminaires.
5. **Die-cast housing:**  
Rugged die-cast aluminum housing for maximum durability.
6. **Mounting:**  
24" Wood Pole Arm (ships in master carton with fixture)
7. **IP66 rated light engine:**  
Reliable light engines that are IP66 sealed to protect against dust and moisture to protect the life of the LED.
8. **Optional prismatic drop lens:**  
Allows the fixture to serve as a beacon to be seen from a distance.
9. **Drivers:**  
The dimming driver 0-10V is standard and D4i certified drivers are optional, enabling controls to be added now or in the future.