

# Boundless possibilities. Exceptional results.

# Introducing Gardco GeoForm wall sconces


### **Minimalist design,** featuring six shapes












### Groundbreaking LED technology

**Two light engines** to tackle any task





### Wall sconce: transformed

GeoForm offers six distinct luminaire shapes to pair with buildings large and small, modern or traditional. Designed around the latest in LED technology, these sconces are small in scale, featuring a minimalistic daytime aesthetic. At night, GeoForm sconces combine best-in-class pathway lighting with specialized optics to highlight any façade.


#### **Product highlights**

- Wedge, block and cylinder shapes in two sizes for any application
- Two light engines suitable for any task
- Best in class efficacy from 150 to 178 lumens per watt
- Light weight for ease of installation
- Modern geometric designs at a small scale

# Illumination: revolutionized

With two distinct light engines, you can highlight building features, or provide best-in-class pathway illumination. The choice is yours and you no longer need different luminaires to do it.






### **Light Effects optics**


Uplighting or downlighting

Lumen output ranging from 700 to 2,400

## Distributions


### **Precision Plus**





Type 2

Туре 3



Type 4

### **Light Effects**

Spot

#### Light Effects - Down

Pencil

Wall Wash





# Light Effects - Up Pencil Spot Wall Wash

#### Light Effects - Up and down

 Wall Wash
 Pencil
 Spot

 Main Wash
 Pencil
 Spot

6 gardcolighting.com/geoform

# Light engine offering

### **Precision Plus**




Luminaire	Small Wedge	Small Block	Small Cylinder	Medium Wedge	Medium Block	Medium Cylinder
Precision Plus	✓	~	<ul> <li>✓</li> </ul>	<ul> <li>Image: A second s</li></ul>	<ul> <li>Image: A second s</li></ul>	~
Diffuse Lens	~	~	-	-	-	-

### Light Effects





Luminaire	Small Wedge	Small Block	Small Cylinder	Medium Wedge	Medium Block	Medium Cylinder
Light Effects	-	✓	✓	-	✓	~
Uplight - wet location	-	~	~	-	~	~
Up and downlight	-	-	-	-	~	~





# **Small Wedge**


#### **Lumens** 1,700-6,500


**Efficacy** 130-175

**Optical Distributions** Type 2, 3, 4, diffuse Emergency Standard (0-40°C)

**Mounting Orientation** Down only

Mounting Height 8-12'





### **Product highlight**



Diffuse lens option available for over doorway applications

6lbs



10 gardcolighting.com/geoform

# **Medium Wedge**


Lumens 1,700-12,000

**Efficacy** 140-180

**Optical Distributions** Type 2, 3, 4 Emergency Standard (0-40°C)

**Mounting Orientation** Down only

Mounting Height 10-24'







# **Small Block**

#### Lumens 1,700-6,500


Efficacy 130-175

**Optical Distributions** Precision plus: type 2, 3, 4, diffuse Light effects: wall wash, spot, pencil Emergency Standard (0-40°C)

**Mounting Orientation** Down or up

**Mounting Height** 8-12'









# **Medium Block**


Lumens 2,900-12,700


**Efficacy** 140-180

**Optical Distributions Precision plus:** type 2, 3, 4 **Light effects:** wall wash, spot, pencil Emergency Cold rated (-20-40°C)

**Mounting Orientation** Down, up, down and up

Mounting Height 10-24'





#### **Product highlights**



Light effects option available



Option to mount down, up, or both



# **Small Cylinder**

**Lumens** 1,700-6,500


**Efficacy** 130-175

**Optical Distributions Precision plus:** type 2, 3, 4 **Light effects:** wall wash, spot, pencil Emergency Standard (0-40°C)

**Mounting Orientation** Down or up

Mounting Height 8-12'





#### **Product highlight**



Light effects option available



Option to mount down or up













# **Medium Cylinder**

Lumens 2,900-6,500

Efficacy 130-175

**Optical Distributions** Precision plus: type 2, 3, 4 Light effects: wall wash, spot, pencil Emergency Cold rated (-20-40°C)

**Mounting Orientation** Down, up, down and up

**Mounting Height** 8-12'





### Take your GeoForm to the next level

With up to 178 lumens per watt, switching to GeoForm alone will result in significant energy savings. If additional controls are required, GeoForm offers a range of basic to advanced options to meet your needs.

### **Basic controls**

#### 0-10V Dimming

GeoForm luminaires include 0-10V dimming drivers standard. Dimming leads can be accessible for controls by others.

#### Photocell

All GeoForm luminaires are available with a button photocell option for basic daylight sensing capability.

#### **Motion Response**

GeoForm wedge and block medium are available with a microwave motion sensor.

### Automatic Profile Dimming with Dynadimmer

Dynadimmer reduces the luminaire's light output according to pre-programmed or customized dimming schedules to reduce light pollution and energy consumption without compromise.

#### Emergency


All GeoForm luminaires feature integral emergency battery backup. The medium sizes are available with cold pack. No back box is required.



## It's all about control

#### Make the leap from smart lighting to super smart lighting

Connectivity is the future and key to unlocking your smart building potential. Help boost your energy savings, reach your sustainability targets, and enhance occupancy comfort levels immediately. Interact is a connected system with wireless luminaire level controls and integral occupancy & daylight sensing.



# Start simple and lay the foundation

- Smart lighting with luminaire integrated occupancy and daylight sensor.
- Save up to 80% on installation and material cost compared with more complex systems.<sup>1</sup>
- 1. Compared to wired networked lighting control systems.

### Features

- No additional wiring required during installation.
- Motion, daylight sensing and grouping can be done right out of the box.
- A gateway can be added at any time for additional features, such as scheduling and remote management.
- Set up is simple and can be done from your smart phone.
- Interact delivers a consistent experience between indoor and outdoor lighting control.
- Interact is the only system that offers wireless connectivity and control for lamps, luminaries, and retrofit kits.





## Simplify servicing with industry unique Service Tag product support



For further peace of mind, GeoForm sconces are backed by our exclusive Service Tag, which includes quick registration, access to luminaire configurations, and spare parts identification, for assistance throughout the life of the product.



# Streamline your design with Gardco GeoForm

Lighting designers need to fulfill basic functional requirements driven by standards, but also create aesthetically pleasing spaces with light. With Gardco GeoForm, you can capture the best of both worlds by blending performance level capabilities with accent effects to beautifully highlight building materials and surfaces.

For more information, please visit the Gardco GeoForm website at www.gardco.com/geoform



### Signify

© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Signify North America Corporatio 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone 855-486-2216

All trademarks are owned by Signity Holding or their respecti