



Your heavy duty lighting solution

RoadFocus Plus Security Light is your most reliable and affordable solution for rural roads and trails, farm yards, industrial parks and countless other general lighting applications. These areas require dependable, high quality lighting that is IP66 rated, easy to install and maintain. Lumec brings you a hard-working, die-cast utility light that is built to last. Available with multiple optical distributions, RoadFocus Plus Security has dark sky compliant configurations with zero upright. This family also includes Service Tag, which enables data delivery and information sharing, and provides access to assistance throughout the life of the product.

Enhanced performance

Quality and reliability to improve sense of security

Flexible use

Multiple lumen packages and optic options

Built to last

Die-cast aluminum housing and optional aluminum arm and bracket

Reduced Light Pollution

Dark Sky compliant configurations available

Designed to save you money

Outstanding efficacy translates to energy savings

Controls Ready


Features a 7-pin receptacle with dimming driver

RPRS RoadFocus Plus

LED Security Light

A hard-working, die-cast utility light that is built to last

RoadFocus Plus LED Security Light is a reliable and affordable solution for countless general lighting applications. Connectable ready, the RoadFocus Plus Security Light offers multiple lumen packages with industry leading efficacy.



Ideal for a wide variety of locations

- Pole mounted security
- Residential or Rural streets
- Industrial park/warehouses
- Parking lots
- Farm yards
- Boat docks/marinas
- Rural access drives/pathways
- Public trails

Key benefits include

- Enhanced performance
- Low maintenance
- Reliable/built to last
- Worry-Free operation
- Heavy duty
- Affordable
- Outstanding energy efficiency
- Dark Sky rated configurations*

* IDA approved if ordered with 3000K CCT and without refractor.



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.