



# StyliD Evo

## ST780Z HOVL-H

### ST780Z | StyliD Evo Performance Accessory

With StyliD Evo, retailers can enjoy the superior quality of light and market-leading energy efficiency of PerfectAccent optics in a series of flexible and future-proof projectors. StyliD Evo projectors are easy to reconfigure with quick and easy optic upgrades that require no tools. They also support frequent changes in store layouts, as the StyliD Evo projector can be easily repositioned on the track or Maxos fusion backbone. Covering a wide range of lighting applications, from lower light levels in convenience formats to high-ceiling installations where very high light output is required, StyliD offers continuity for every retail concept. StyliD Evo can be mounted on 3C or DALI track (ST770T, ST780T), on Maxos fusion (ST770S, ST780S, ST770X), or into the ceiling with a semi-recessed version (ST770B). All StyliD Evo projectors with PerfectAccent reflectors are certified as a circular lighting product and offer multiple system integration and dimming options, including wired as well as wireless. For prolonged shelf life and better visual representation of food, reducing food waste and increasing sales, fresh food LED lighting recipes are available. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

### Warnings and Safety

- All photometrical data is calculated without optional front glass. Flux should be reduced by 3.5% when using a front glass
- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth.
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

### Product data

# StyliD Evo

## General Information

Value ladder	Specification
--------------	---------------

## Mechanical and Housing

Overall height	70 mm
Overall diameter	100 mm
Mech. impact protection code	IK02 [0.2 J standard]
Accessory color	-
Net Weight (Piece)	0.100 kg

## Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

## Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
--------------------------------------------	--------------------------

Packaging Recyclable content ratio	Cardboard recycling rate > 80%
------------------------------------	--------------------------------

Packaging Material	Cardboard
--------------------	-----------

## Product Data

Order product name	ST780Z HOVL-H
Full product name	ST780Z HOVL-H
Full product code	871869996954700
Order code	910505100824
Material Nr. (12NC)	910505100824
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699969547
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699969547
Product family code	ST780Z [StyliD Evo Performance Accessory]

