


9MX056 EC7 (10PCS)

910606293921



Maxos accessories, Normal, 9MX056 | ACC MAXOS

The swivel device is a versatile mechanical connecting device for Maxos TL-D and TL5 light-lines and enables variable angles between the light-lines. The minimum angle is 45 degrees. Due to its attractive design it is often used in application areas such as shops, schools and museums. Up to four light-lines can be connected with one swivel device. The housing is made of plastic, with a white or silver coating, and with inner supporting elements made of steel. If needed, the swivel device can accommodate lighting control sensors, loudspeakers, etc. It is pre-mounted with an adjustable quick hanger with a 1.25m steel suspension wire. One dedicated coupling piece (9MX056 CP-SD WH/SI) per trunking section is necessary to connect the trunking to the swivel device. Electrical components for mains feed-through have to be ordered as required.

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I

Mechanical and Housing

Ingress protection code	-
Accessory colour	-
Net Weight (Piece)	0.060 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	IIII9_9MX056I_0003.PDF	Download 

Product Data

Order product name	9MX056 EC7 (10PCS)
Full product name	9MX056 EC7 (10PCS)
Full EOC	403073203217400
Local code description	MAXTB10
Order code	910606293921
Material no. (12 NC)	910606293921
Local order code	MAXTB10
Numerator – quantity per pack	1
EAN/UPC — Product/Case	4030732032174
Numerator – packs per outer box	1
EAN/UPC - Case	4030732032174
Product family code	9MX056 [ACC MAXOS]