



Maxos fusion

LL500Z MB-SW2 L5000 WH

LL500Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information		Material	
Service tag	Yes	Ingress protection code	-
Value ladder	Specification	Mech. impact protection code	-
Accessory color		White	
Net Weight (Piece)		0.124 kg	
Approval and Application			
CE mark		Yes	
EU RoHS compliant		Yes	
Product Data			
Order product name		LL500Z MB-SW2 L5000 WH	
Full product name		LL500Z MB-SW2 L5000 WH	
Full product code		871869637457399	

Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

Mechanical and Housing	
Overall length	180 mm
Overall width	120 mm
Overall height	40 mm
Dimensions (Height x Width x Depth)	40 x 120 x 180 mm

Maxos fusion

Order code	910925864230
Material Nr. (12NC)	910925864230
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696374573
Numerator - Packs per outer box	20

EAN/UPC - Case	8718696383483
Product family code	LL500Z [Maxos fusion Acc.]

Dimensional drawing

