



Maxos fusion

LL500Z MB-SW2 L5000 SI

LL500Z | Maxos fusion Acc., Silver

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information		Material	
Service tag	Yes	Material	Steel
Value ladder	Specification	Ingress protection code	-
Operating and Electrical		Mech. impact protection code	-
Input Voltage	- V	Accessory color	Silver
Line Frequency	- Hz	Net Weight (Piece)	0.124 kg
Protection class IEC	-	Approval and Application	
Mechanical and Housing		CE mark	Yes
Overall length	180 mm	EU RoHS compliant	Yes
Overall width	120 mm	Product Data	
Overall height	40 mm	Order product name	LL500Z MB-SW2 L5000 SI
Dimensions (Height x Width x Depth)	40 x 120 x 180 mm	Full product name	LL500Z MB-SW2 L5000 SI
		Full product code	871869637458099

Maxos fusion

Order code	910925864231
Material Nr. (12NC)	910925864231
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696374580
Numerator - Packs per outer box	20

EAN/UPC - Case	8718696383490
Product family code	LL500Z [Maxos fusion Acc.]

Dimensional drawing

