



# Maxos fusion

## LL500Z CB-CH WH

LL500Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

### Product data

General Information		Material	
Service tag	Yes	Ingress protection code	-
Value ladder	Specification	Mech. impact protection code	-
Operating and Electrical		Accessory color	White
Input Voltage	- V	Net Weight (Piece)	0.081 kg
Line Frequency	- Hz	Approval and Application	
Protection class IEC	-	CE mark	Yes
Mechanical and Housing		EU RoHS compliant	Yes
Overall length	120 mm	Product Data	
Overall width	40 mm	Order product name	LL500Z CB-CH WH
Overall height	40 mm	Full product name	LL500Z CB-CH WH
Dimensions (Height x Width x Depth)	40 x 40 x 120 mm	Full product code	871869637460399

## Maxos fusion

Order code	910925864233
Material Nr. (12NC)	910925864233
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696374603
Numerator - Packs per outer box	15

EAN/UPC - Case	8718696383513
Product family code	LL500Z [Maxos fusion Acc.]

### Dimensional drawing

