



# Maxos fusion

## LL500Z SPA-CD

LL500Z | Maxos fusion Acc., Steel

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

### Product data

General Information		Material	
Service tag	Yes	Ingress protection code	-
Value ladder	Specification	Mech. impact protection code	-
Accessories		Accessory color	Steel
Operating and Electrical		Net Weight (Piece)	0.018 kg
Input Voltage	- V	Approval and Application	
Line Frequency	- Hz	CE mark	Yes
Protection class IEC	-	EU RoHS compliant	Yes
Mechanical and Housing		Product Data	
Overall length	65 mm	Order product name	LL500Z SPA-CD
Overall width	40 mm	Full product name	LL500Z SPA-CD
Overall height	25 mm	Full product code	871869637463499
Dimensions (Height x Width x Depth)	25 x 40 x 65 mm		

## Maxos fusion

Order code	910925864239
Material Nr. (12NC)	910925864239
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696374634
Numerator - Packs per outer box	40

EAN/UPC - Case	8718696383575
Product family code	LL500Z [Maxos fusion Acc.]

### Dimensional drawing

