



Maxos fusion

LL500Z BC L285 WH

LL500Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information	
Service Tag	Yes
Value ladder	Specification
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-
Mechanical and Housing	
Overall length	285 mm
Overall width	60 mm
Overall height	8.5 mm
Dimensions (height x width x depth)	9 x 60 x 285 mm

Material	Polycarbonate
Ingress protection code	-
Mech. impact protection code	-
Accessory colour	White
Net Weight (Piece)	0.023 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Product Data	
Order product name	LL500Z BC L285 WH
Full product name	LL500Z BC L285 WH
Full EOC	871869698957999

Maxos fusion

Order code	910925864513
Material no. (12 NC)	910925864513
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696989579
Numerator – packs per outer box	20

EAN/UPC - Case	8718696987445
Product family code	LL500Z [Maxos fusion Acc.]

Dimensional drawing

