



Maxos fusion

LL600Z BC L2180 WH

LL600Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information		Ingress protection code	
Value ladder	Specification		-
Operating and Electrical		Mech. impact protection code	
Input Voltage	- V		-
Line Frequency	- Hz	Accessory colour	White
Protection class IEC	-	Net Weight (Piece)	0.180 kg
Mechanical and Housing		Approval and Application	
Overall length	2,180 mm	CE mark	Yes
Overall width	60 mm	EU RoHS compliant	Yes
Overall height	8.5 mm	Product Data	
Dimensions (height x width x depth)	9 x 60 x 2180 mm	Order product name	LL600Z BC L2180 WH
Material	Polycarbonate	Full product name	LL600Z BC L2180 WH
		Full EOC	871869698950099
		Order code	910925864763

Maxos fusion

Material no. (12 NC)	910925864763
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696989500
Numerator – packs per outer box	32

EAN/UPC - Case	8718696987377
Product family code	LL600Z [Maxos fusion Acc.]

Dimensional drawing

