



Maxos fusion

LL600Z BC L520 WH

LL600Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information	
Value ladder	Specification

Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

Mechanical and Housing	
Overall length	520 mm
Overall width	60 mm
Overall height	8.5 mm
Dimensions (Height x Width x Depth)	9 x 60 x 520 mm
Material	Polycarbonate

Ingress protection code	-
Mech. impact protection code	-
Accessory color	White
Net Weight (Piece)	0.043 kg

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes

Product Data	
Order product name	LL600Z BC L520 WH
Full product name	LL600Z BC L520 WH
Full product code	871869698947099
Order code	910925864956

Maxos fusion

Material Nr. (12NC)	910925864956
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696989470
Numerator - Packs per outer box	8

EAN/UPC - Case	8718696987346
Product family code	LL600Z [Maxos fusion Acc.]

Dimensional drawing

