



Maxos fusion

LL600Z BC L1090 WH

LL600Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information		Ingress protection code	
Value ladder	Specification		-
		Mech. impact protection code	
			-
		Accessory colour	
			White
		Net Weight (Piece)	
			0.090 kg
Operating and Electrical		Approval and Application	
Input Voltage	- V	CE mark	Yes
Line Frequency	- Hz	EU RoHS compliant	Yes
Protection class IEC	-		
Mechanical and Housing		Product Data	
Overall length	1,090 mm	Order product name	LL600Z BC L1090 WH
Overall width	60 mm	Full product name	LL600Z BC L1090 WH
Overall height	8.5 mm	Full EOC	871869698949499
Dimensions (height x width x depth)	9 x 60 x 1090 mm	Order code	910925864958
Material	Polycarbonate		

Maxos fusion

Material no. (12 NC)	910925864958
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696989494
Numerator – packs per outer box	32

EAN/UPC - Case	8718696987360
Product family code	LL600Z [Maxos fusion Acc.]

Dimensional drawing

