



# Maxos fusion

## LL500Z BA WH

LL500Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

### Product data

| General Information      |                | Dimensions (Height x Width x Depth)        |                          |
|--------------------------|----------------|--|--------------------------|
| Service tag              | Yes            | Material                                   | Steel                    |
| Value ladder             | Specification  | Ingress protection code                    | IP20 [Finger-protected]  |
| Operating and Electrical |                | Mech. impact protection code               | IK02 [0.2 J standard]    |
| Input Voltage            | 220 to 240 V   | Accessory color                            | White                    |
| Line Frequency           | 50 to 60 Hz    | Angle                                      | 0°                       |
| Protection class IEC     | Safety class I | Net Weight (Piece)                         | 0.370 kg                 |
| Mechanical and Housing   |                | Approval and Application                   |                          |
| Overall length           | 309.4 mm       | CE mark                                    | Yes                      |
| Overall width            | 62.3 mm        | EU RoHS compliant                          | Yes                      |
| Overall height           | 14.7 mm        | Sustainability Data                        |                          |
| Overall diameter         | 0 mm           | Non-virgin material ratio of the packaging | Cardboard > 80% recycled |

## Maxos fusion

|                                    |                                |
|------------------------------------|--------------------------------|
| Packaging Recyclable content ratio | Cardboard recycling rate > 80% |
| Packaging Material                 | Cardboard                      |
| <b>Product Data</b>                |                                |
| Order product name                 | LL500Z BA WH                   |
| Full product name                  | LL500Z BA WH                   |
| Full product code                  | 871869699833500                |
| Order code                         | 910925865356                   |

|                                 |                            |
|---------------------------------|----------------------------|
| Material Nr. (12NC)             | 910925865356               |
| Numerator - Quantity Per Pack   | 1                          |
| EAN/UPC - Product/Case          | 8718696998335              |
| Numerator - Packs per outer box | 1                          |
| EAN/UPC - Case                  | 8718696998335              |
| Product family code             | LL500Z [Maxos fusion Acc.] |

### Dimensional drawing

