



Maxos fusion

LL500Z BA SI

LL500Z | Maxos fusion Acc., Silver

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information		Dimensions (Height x Width x Depth)	
Service tag	Yes	Material	Steel
Value ladder	Specification	Ingress protection code	IP20 [Finger-protected]
Operating and Electrical		Mech. impact protection code	IK02 [0.2 J standard]
Input Voltage	220 to 240 V	Accessory color	Silver
Line Frequency	50 to 60 Hz	Angle	-
Protection class IEC	Safety class I	Net Weight (Piece)	0.370 kg
Mechanical and Housing		Approval and Application	
Overall length	309.4 mm	CE mark	Yes
Overall width	62.3 mm	EU RoHS compliant	Yes
Overall height	14.7 mm	Product Data	
Overall diameter	0 mm	Order product name	LL500Z BA SI

Maxos fusion

Full product name	LL500Z BA SI
Full product code	871869699835900
Order code	910925865358
Material Nr. (12NC)	910925865358
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696998359

Numerator - Packs per outer box	1
EAN/UPC - Case	8718696998359
Product family code	LL500Z [Maxos fusion Acc.]

Dimensional drawing

