

SP340Z EPESS WH

910925867440



- V, White

Philips FlexBlend is an attractive family of surface mounted and suspended luminaires, next to Flexblend recessed. The luminaire range is enabling building owners to advance their lighting operations, by offering office-compliant lighting with a return on investment of less than 3 to 4 years. FlexBlend provides the required flexibility through the adaptability in design. This gives the possibility to install the luminaires easily in the field, at any moment. Even when today's luminaire is suspended, tomorrow this can be adapted to a surface mounted installation at the venue. And the other way around. . The surface mounted and suspended luminaire range fit to many different office spaces like open plan office, corridors, reception or meeting rooms. FlexBlend is offered in both lines and as standalone, using the same lighting module. This gives the option to the users to use FlexBlend as standalone now,

and tomorrow, as line. The controller is integrated in the luminaire. As technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations that can help optimize operations further. For this reason, FlexBlend holds all connectivity and future ready options available. As System Ready luminaire it can be paired with lighting management systems such as the Philips SpaceWise, and to software-based lighting systems as Interact Office wired (PoE) and Interact Office wireless and/or existing and upcoming sensor innovations. The luminaire range is therefore future ready and can be delivered without any system component, and in a next phase, in the field to be upgraded. An attractive opportunity for new installations and renovations.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If The above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

General Information

Service tag	Yes
Value ladder	Performance

Operating and Electrical

Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

Mechanical and Housing

Overall height	70 mm
Material	Polycarbonate
Ingress protection code	-
Mech. impact protection code	-
Accessory color	White
Angle	-
Net Weight (Piece)	0.250 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	SP340Z EPESS WH
Full product name	SP340Z EPESS WH
Full product code	871951410698700
Order code	910925867440
Material Nr. (12NC)	910925867440
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514106987
Numerator - Packs per outer box	1

EAN/UPC - Case	8719514106987
Product family code	SP340Z [FLEXBLEND S&S ACCESSORIES]

Related Documents

Documents and certificates	Document Name	Download
Tender text	Tender_Text_910925867440_en_AA.txt	Download 

