PHILIPS

VGP703 40 4S 730 24V III DM10 42/60S

910925868310

Luma gen2 Solar, Road & street light, 3000 K, CRI70, Distribution medium 10, Safety class III, IP66

Road & street light, Aluminum die cast, Dark gray, Side-entry for diameter 42 to 60 mm, 3000 K, (0.434, 0.403) SDCM <5, CRI70, Distribution medium 10, IP66 | Dust penetration-protected, jet-proof, IK10 | 20 J vandal-resistant, Safety class III, Connection unit 2-pole

General Information

Light source replaceable	Yes
Driver included	No
Light source engine type	LED
Service tag	Yes
Warranty period	5 years

Light Technical

Upward light output ratio	0
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	70
Number of light sources	1

Light source color	730 warm white
Luminaire light beam spread	155° x 86°
Optic type outdoor	Distribution medium 10
Effective projected area	0.0998 m²

Operating and Electrical

Input Voltage	24 V
Connection	Connection unit 2-pole
Cable	-
Protection class IEC	Safety class III
Surge Protection (Common/ Differential)	-

Controls and Dimming

Dimmable	No
Configurability	Configurable
Control interface	-
Solar dimming profile	configurable via charge controller

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polymethyl methacrylate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Side-entry for diameter 42 to 60 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	734 mm
Overall width	295 mm
Overall height	146 mm
Dimensions (Height x Width x Depth)	146 x 295 x 734 mm
Battery location	on-pole, in-ground
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Standard tilt angle posttop	-
Standard tilt angle side entry	0°
Optical cover type	Glass
Net Weight (Piece)	8.400 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.434, 0.403) SDCM <5
Init. Color Rendering Index Tolerance	+/-2
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L98

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Embedded carbon (A1-A3)	187 kg CO_2e
Product non-virgin material ratio	7.05 %
Recyclable content ratio of the finished product	66.3 %
GWP total B6 (kg CO2eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO2eq / kwh)
GWP total B6 (kg CO2eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO2 eq / kwh)
Non-virgin material ratio of the packaging	Cardboard > 80% recycled

Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	VGP703 40 4S 730 24V III DM10 42/60S
Full product name	VGP703 40 4S 730 24V III DM10 42/60S

Full product code	871951462374300
Order code	62374300
Material Nr. (12NC)	910925868310
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514623743
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514623743
Product family code	VGP703 [LUMA GEN2 MINI SOLAR]

Dimensional drawing



Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	SIG-583442710541430-Lumagen2solar-INI.pdf	Download

Photometry and lighting design	Document Name	Download
ROLF File	OFDM2_VGP703T251xLED74-4S730DM10.ROLF	Download
LDT File	OFMT2_VGP703T251xLED74-4S730DM10.LDT	Download
ULD File	OFDM1_VGP703T251xLED74-4S730DM10.ULD	Download

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.