

SP350Z EP WH

910925868341



- V, White

These days, many office owners and office lighting designers prefer lines of light. The reason is simple. Not only do light lines come in a minimalistic design; they also offer far more choice and flexibility. Short or long lines and luminaires, standalone luminaires, different optics including asymmetric, different shapes and even a variety of colors; anything is possible. And with KeyLine, all these benefits come at a competitive price while still complying with office lighting norms. KeyLine is a superb light line range with a slim, minimalistic design and a high lumen output to illuminate the brightest office spaces. But with comfortable, low levels of glare it's also easy on the eye and complies with UGR19. That makes KeyLine ideal for linear applications, as well as standalone suspended or surface-mounted luminaires (Accessories to be ordered separately). A range that offers the ultimate flexibility and unlimited possibilities. KeyLine design flexibility comes in the form of different lengths, colors and light outputs - including L-shapes, as well as straight lines. All with high efficiency up to 142 lm/W, and the option to upgrade with wireless connectivity and control. Add to that attractive pricing, and with KeyLine you can also enjoy excellent value that ensures a superb total cost of ownership.

Warnings and Safety

- KeyLine luminaires have an IP20 classification and are not protected against water ingress. We strongly recommend that the installation environment is checked for suitability.
- If – despite the IPX0 classification warning – luminaires are subject to water ingress, Philips and Signify cannot guarantee safety or prevent failure. In this case the product warranty does not apply and becomes void.

General Information

Value ladder	Performance
--------------	-------------

Operating and Electrical

Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

Mechanical and Housing

Overall length	70 mm
Overall width	2.5 mm
Overall height	70 mm
Dimensions (Height x Width x Depth)	70 x 3 x 70 mm
Material	Steel
Ingress protection code	-
Mech. impact protection code	-
Accessory color	White
Angle	-
Net Weight (Piece)	0.225 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Related Documents

Documents and certificates	Document Name	Download
Tender text	Tender_Text_910925868341_en_SA.txt	Download 
Installation Instructions	KeyLine-InstallationInstruction.pdf	Download 

Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	SP350Z EP WH
Full product name	SP350Z EP WH
Full product code	871951462405400
Order code	910925868341
Material Nr. (12NC)	910925868341
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514624054
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514624054
Product family code	SP350Z [KeyLine]

