



KeyLine, Surface & Suspended

SP350Z CP

SP350Z | KeyLine, - V

These days, many office owners and office lighting designers prefer lines of light. The reason is simple. Not only do light lines come in a minimalistic design; they also offer far more choice and flexibility. Short or long lines and luminaires, standalone luminaires, different shapes and even a variety of colours; anything is possible. And with KeyLine, all these benefits come at a competitive price while still complying with office lighting norms. KeyLine is a superb light line range with a slim, minimalistic design and a high lumen output to illuminate the brightest office spaces. But with comfortable, low levels of glare it's also easy on the eye and complies with UGR19. This makes KeyLine ideal for linear applications, as well as standalone suspended or surface-mounted luminaires. A range that offers the ultimate flexibility and unlimited possibilities. KeyLine design flexibility comes in the form of different lengths, colours and light outputs – including L-shapes, as well as straight lines. All with high efficiency up to 130 lm/W, and the option to upgrade with wireless connectivity and control. Add to that attractive pricing, and with KeyLine you can also enjoy excellent value that ensures a superb total cost of ownership.

Warnings and Safety

- KeyLine luminaires have an IP20 classification and are not protected against water ingress. We strongly recommend that the installation environment is checked for suitability.
- If – despite the IPX0 classification warning – luminaires are subject to water ingress, Philips and Signify cannot guarantee safety or prevent failure. In this case the product warranty does not apply and becomes void.

Product data

KeyLine, Surface & Suspended

General Information	
Value ladder	Performance
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-
Mechanical and Housing	
Material	Steel
Ingress protection code	-
Mech. impact protection code	-
Accessory colour	-
Angle	-
Net Weight (Piece)	0.300 kg
Approval and Application	
CE mark	Yes

EU RoHS compliant	Yes
Product Data	
Order product name	SP350Z CP
Full product name	SP350Z CP
Full EOC	871951462408500
Order code	910925868344
Material no. (12 NC)	910925868344
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514624085
Numerator – packs per outer box	1
EAN/UPC - Case	8719514624085
Product family code	SP350Z [KeyLine]

