



# Maxos unify

## LL554T 4x2.5+8x1.5 Gen2 WH

LL554T | Maxos unify rail 4430mm, IP20 | Finger-protected

An adaptable LED trunking system, combining the well proven advantages of an electrical track which allows flexible positioning of linear panels offering multiple flux/ length combinations with specially designed lenses to direct the light where needed. A solution allowing for new projects to be designed with optimal number of linear panels and a solution for retrofitting old installations - Bringing your application right up to date with the latest lighting possibilities. Now, and in the future.

### Product data

<b>General Information</b>	
Value ladder	Specification
<b>Mechanical and Housing</b>	
Overall height	42 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	5.700 kg
<b>Approval and Application</b>	
CE mark	Yes
EU RoHS compliant	Yes
<b>Sustainability Data</b>	
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%

Packaging Material	Cardboard
<b>Product Data</b>	
Order product name	LL554T 4x2.5+8x1.5 Gen2 WH
Full product name	LL554T 4x2.5+8x1.5 Gen2 WH
Full product code	872016996484699
Order code	910925870299
Material Nr. (12NC)	910925870299
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169964846
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169476240
Product family code	LL554T [Maxos unify rail 4430mm]

# Maxos unify

## Dimensional drawing

