



Maxos unify

LL552T 4x2.5+2x1.5 Gen2 BK

LL552T | Maxos unify rail 2215mm, IP20 | Finger-protected

An adaptable LED trunking system, combining the well proven advantages of an electrical track which allows flexible positioning of linear panels offering multiple flux/ length combinations with specially designed lenses to direct the light where needed. A solution allowing for new projects to be designed with optimal number of linear panels and a solution for retrofitting old installations - Bringing your application right up to date with the latest lighting possibilities. Now, and in the future.

Product data

General Information		Packaging Material	Cardboard
Value ladder	Specification		
Mechanical and Housing		Product Data	
Overall height	42 mm	Order product name	LL552T 4x2.5+2x1.5 Gen2 BK
Ingress protection code	IP20 [Finger-protected]	Full product name	LL552T 4x2.5+2x1.5 Gen2 BK
Mech. impact protection code	IK02 [0.2 J standard]	Full product code	872016996488499
Net Weight (Piece)	2.860 kg	Order code	910925870821
Approval and Application		Material Nr. (12NC)	910925870821
CE mark	Yes	Numerator - Quantity Per Pack	1
EU RoHS compliant	Yes	EAN/UPC - Product/Case	8720169964884
Sustainability Data		Numerator - Packs per outer box	10
Non-virgin material ratio of the packaging	Cardboard > 80% recycled	EAN/UPC - Case	8720169954748
Packaging Recyclable content ratio	Cardboard recycling rate > 80%	Product family code	LL552T [Maxos unify rail 2215mm]

Maxos unify

Dimensional drawing

