



Maxos unify

LL552T 4x2.5+8x1.5 Gen2 BK

LL552T | Maxos unify rail 2215mm, IP20 | Finger-protected

An adaptable LED trunking system, combining the well proven advantages of an electrical track which allows flexible positioning of linear panels offering multiple flux/ length combinations with specially designed lenses to direct the light where needed. A solution allowing for new projects to be designed with optimal number of linear panels and a solution for retrofitting old installations - Bringing your application right up to date with the latest lighting possibilities. Now, and in the future.

Product data

General Information	
Value ladder	Specification
Mechanical and Housing	
Overall height	42 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	3.010 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Sustainability Data	
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%

Packaging Material	Cardboard
Product Data	
Order product name	LL552T 4x2.5+8x1.5 Gen2 BK
Full product name	LL552T 4x2.5+8x1.5 Gen2 BK
Full product code	872016996490799
Order code	910925870823
Material Nr. (12NC)	910925870823
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169964907
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169954762
Product family code	LL552T [Maxos unify rail 2215mm]

Maxos unify

Dimensional drawing

