



# Maxos unify

## LL554T 4x2.5+8x1.5 Gen2 BK

LL554T | Maxos unify rail 4430mm, IP20 | Finger-protected

An adaptable LED trunking system, combining the well proven advantages of an electrical track which allows flexible positioning of linear panels offering multiple flux/ length combinations with specially designed lenses to direct the light where needed. A solution allowing for new projects to be designed with optimal number of linear panels and a solution for retrofitting old installations - Bringing your application right up to date with the latest lighting possibilities. Now, and in the future.

### Product data

General Information	
Value ladder	Specification
Mechanical and Housing	
Overall height	42 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	5.820 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Sustainability Data	
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%

Packaging Material	Cardboard
Product Data	
Order product name	LL554T 4x2.5+8x1.5 Gen2 BK
Full product name	LL554T 4x2.5+8x1.5 Gen2 BK
Full product code	872016996496999
Order code	910925870829
Material Nr. (12NC)	910925870829
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169964969
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169954823
Product family code	LL554T [Maxos unify rail 4430mm]

## Maxos unify

### Dimensional drawing

