



# 3-circuit Square RCS750

## RCS750 3C L1000 BK (XTS4100-2)

3-circuit Square RCS750, Normal, Black, IP30 | Tool-protected

The Philips 3-circuit square track system consists of an anodised aluminium profile in natural anodised or painted white in lengths of 1, 2, 3 and 4 m. It contains four electrical conductors allowing easy creation of any required configuration: horizontal or vertical, recessed or surface-mounted, on the wall, on free-standing panels or floating. All luminaires have their separate power supply and can be switched selectively by phase or by circuit. Because the luminaires are easy to move, by simply clicking them in place in the adaptor on the track, changes in the lighting and presentation can be made very simply. All 230V projectors in the Philips range can be installed on this track system. All the associated accessories are common to both the surface-mounted and recessed models and guarantee a good electrical and mechanical connection.

### Product data

Operating and Electrical		CE mark	Yes
Protection class IEC	Safety class I	EU RoHS compliant	Yes
Mechanical and Housing		Product Data	
Overall length	1,000 mm	Order product name	RCS750 3C L1000 BK (XTS4100-2)
Ingress protection code	IP30 [Tool-protected]	Full product name	RCS750 3C L1000 BK (XTS4100-2)
Accessory color	Black	Full product code	871155979851600
Net Weight (Piece)	0.900 kg	Order code	79851600
Approval and Application		Material Nr. (12NC)	910930013218
Glow-wire test	Temperature 850 °C, duration 5 s	Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711559798516

## 3-circuit Square RCS750

---

Numerator - Packs per outer box	1
EAN/UPC - Case	8711559798516

---

### Dimensional drawing

