



GreenSpace Surface Mount

SP303P P6S 940 PSU MB

GreenSpace Surface Mount, 89 lm/W, 940 neutral white

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

General Information		Number of products on MCB of 16 A type B	
Light source engine type	LED	Protection class IEC	Safety class II
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	530 lm	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	89 lm/W		
Color rendering index (CRI)	>90	Mechanical and Housing	
Light source color	940 neutral white	Housing Material	Aluminum Alloy
Operating and Electrical		Optical cover material	Acrylate
Input Voltage	200 to 240 V	Housing Color	White
Line Frequency	50 to 60 Hz	Optical cover finish	Frosted
Power Consumption	5.4 6.6 W	Ingress protection code	IP20 [Finger-protected]
Power Factor (Fraction)	0.5	Mech. impact protection code	IK03 [0.3 J]
		Optical cover type	Acrylate

GreenSpace Surface Mount

Net Weight (Piece)	0.895 kg
Approval and Application	
CE mark	No
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	SP303P P6S 940 PSU MB

Full product name	SP303P P6S 940 PSU MB
Full product code	872016952897099
Order code	911401500122
Material Nr. (12NC)	911401500122
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169528970
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169540460

Dimensional drawing

