



GreenSpace Flex Luna

RS378B P6 930 PSU-E WB M43 WP PRO

GreenSpace Flex Luna, 5.9 W, 930 warm white, IP20/54 |
Finger-protected; dust accumulation-protected, splash-proof

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

General Information		Protection class IEC	
Light source engine type	LED	Safety class II	
Value ladder	Performance	Controls and Dimming	
Light Technical		Dimmable	-
Luminous Flux	545 lm	Control interface	-
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	92 lm/W	Housing Material	Aluminum Alloy
Color rendering index (CRI)	92	Optical cover material	Polycarbonate
Light source color	930 warm white	Housing Color	Black
Unified glare rating CEN	16	Optical cover finish	Structured optic
Operating and Electrical		Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Input Voltage	220 to 240 V	Mech. impact protection code	IK03 [0.35 J reinforced]
Line Frequency	50 or 60 Hz	Optical cover type	Lens
Power Consumption	5.9 W	Net Weight (Piece)	0.160 kg
Power Factor (Fraction)	0.9	Number of products on MCB of 16 A type B 75	

GreenSpace Flex Luna

Approval and Application

CE mark	Yes
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RS378B P6 930 PSU-E WB M43 WP PRO
--------------------	-----------------------------------

Full product name	RS378B P6 930 PSU-E WB M43 WP PRO
Order code	911401500346
Material Nr. (12NC)	911401500346
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

Dimensional drawing

