



GreenPerform Batten G3 BN398C

BN398C LED20/NW L1200 PSU OP

GreenPerform Batten G3 BN398C, 15.8 W, 2400 lm, 4000 K

GreenPerform batten BN398C is a cost competitive linear solution with good performance and multiple lumen output for retail and industry applications. It offers surface mount and suspension installations to cater for different mounting options. Its multiple optic designs accommodate different applications as well.

Product data

General Information		Protection class IEC	
Light source engine type	LED	Protection class IEC	Safety class I
Value ladder	Performance	Controls and Dimming	
Light Technical		Dimmable	No
Luminous Flux	2,400 lm	Control interface	-
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	151 lm/W	Housing Material	Metal-Plastic
Color rendering index (CRI)	>80	Optical cover material	Polymethyl methacrylate
Light source color	840 neutral white	Housing Color	White RAL 9003
Operating and Electrical		Optical cover finish	Frosted
Input Voltage	220-240 V	Overall length	1,135 mm
Line Frequency	50 or 60 Hz	Overall width	58 mm
Inrush current	6 A	Overall height	58 mm
Power Consumption	15.8 W	Dimensions (Height x Width x Depth)	58 x 58 x 1135 mm
Power Factor (Fraction)	0.9	Ingress protection code	IP20 [Finger-protected]
Number of products on MCB of 16 A type B	40	Mech. impact protection code	IK03 [0.35 J reinforced]
		Optical cover type	Polymethyl methacrylate bowl/cover

GreenPerform Batten G3 BN398C

Net Weight (Piece)	1.700 kg
Approval and Application	
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

Product Data	
Order product name	BN398C LED20/NW L1200 PSU OP
Full product name	BN398C LED20/NW L1200 PSU OP
Full product code	692382863909900
Order code	911401501671
Material Nr. (12NC)	911401501671
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828639099
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828639099

Dimensional drawing

