



# LuxSpace Pro

## DN593B LED29/840 P20PSU D200 VWB-M G2

LuxSpace Pro, 20.1 W, 3020 lm, 4000 K, Fixed Output

Philips LuxSpace Pro builds on the LuxSpace family's reputation for superb performance, extremely low energy use, high visual comfort and appearance design. This next generation of reliable LED downlights comes in an elegant design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. LuxSpace Pro is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 450 to 8,000 lumen, 3inch to 8inch, with the option to choose fixed, dimmable, or Interact Ready variants. This makes LuxSpace Pro the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

### Product data

| General Information      |               |
|--------------------------|---------------|
| Light source engine type | LED           |
| Service tag              | Yes           |
| Value ladder             | Specification |

  

| Light Technical                    |                                       |
|------------------------------------|---------------------------------------|
| Luminous Flux                      | 3,020 lm                              |
| Correlated Color Temperature (Nom) | 4000 K                                |
| Luminous Efficacy (rated) (Nom)    | 150 lm/W                              |
| Color rendering index (CRI)        | 80                                    |
| Light source color                 | 840 neutral white                     |
| Optic type                         | High-efficiency reflector medium beam |
| Unified glare rating CEN           | 25                                    |

| Operating and Electrical                 |                 |
|--|-----------------|
| Input Voltage                            | 220-240 V       |
| Line Frequency                           | 50 or 60 Hz     |
| Inrush current                           | 20 A            |
| Inrush time                              | 50 ms           |
| Power Consumption                        | 20.1 W          |
| Power Factor (Fraction)                  | 0.95            |
| Number of products on MCB of 16 A type B | 120             |
| Protection class IEC                     | Safety class II |

  

| Controls and Dimming |              |
|----------------------|--------------|
| Dimmable             | No           |
| Control interface    | Fixed Output |

# LuxSpace Pro

## Mechanical and Housing

|                              |                         |
|------------------------------|-------------------------|
| Housing Material             | Aluminum Alloy          |
| Optical cover material       | Polycarbonate           |
| Housing Color                | White                   |
| Optical cover finish         | Frosted                 |
| Ingress protection code      | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.3 J]            |
| Optical cover type           | Polycarbonate Diffuser  |
| Net Weight (Piece)           | 1.100 kg                |

## Approval and Application

|                           |                 |
|---------------------------|-----------------|
| CE mark                   | Yes             |
| Ambient temperature range | -20 °C to 40 °C |

## Initial Performance (IEC Compliant)

|                         |        |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

|                             |        |
|-----------------------------|--------|
| Power consumption tolerance | +/-10% |
|-----------------------------|--------|

## Product Data

|                                 |                                       |
|---------------------------------|---------------------------------------|
| Order product name              | DN593B LED29/840 P20PSU D200 VWB-M G2 |
| Full product name               | DN593B LED29/840 P20PSU D200 VWB-M G2 |
| Order code                      | 911401501744                          |
| Material Nr. (12NC)             | 911401501744                          |
| Numerator - Quantity Per Pack   | 1                                     |
| Numerator - Packs per outer box | 1                                     |

## Dimensional drawing

