



GreenSpace Surface Mount

SP303P P9S 930 PSU VWB

GreenSpace Surface Mount, 84 lm/W, 930 warm white

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	760 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	84 lm/W
Color rendering index (CRI)	>90
Light source color	930 warm white
Operating and Electrical	
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	8.1 9.9 W
Power Factor (Fraction)	0.5

Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Acrylate
Housing Color	White
Optical cover finish	Frosted
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Acrylate

GreenSpace Surface Mount

Net Weight (Piece)	0.895 kg
Approval and Application	
CE mark	No
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	SP303P P9S 930 PSU VWB

Full product name	SP303P P9S 930 PSU VWB
Full product code	872016953189599
Order code	911401503522
Material Nr. (12NC)	911401503522
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169531895
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169543386

Dimensional drawing

