



GreenSpace Surface Mount

SP303P P9S 950 PSU NB

GreenSpace Surface Mount, 78 lm/W, White

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

General Information		Number of products on MCB of 16 A type B	
Light source engine type	LED		-
Value ladder	Performance	Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	700 lm	Dimmable	No
Correlated Color Temperature (Nom)	5000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	78 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>90	Housing Material	Aluminum Alloy
Light source color	White	Optical cover material	Acrylate
Operating and Electrical		Housing Color	White
Input Voltage	200 to 240 V	Optical cover finish	Frosted
Line Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
Power Consumption	8.1 9.9 W	Mech. impact protection code	IK03 [0.3 J]
Power Factor (Fraction)	0.5	Optical cover type	Acrylate

GreenSpace Surface Mount

Net Weight (Piece)	0.895 kg
--------------------	----------

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	SP303P P9S 950 PSU NB
--------------------	-----------------------

Full product name	SP303P P9S 950 PSU NB
Full product code	872016952399999
Order code	52399999
Material Nr. (12NC)	911401504422
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169523999
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169535480

Dimensional drawing

