



GreenPerform Waterproof G3

WT198C LED60S/840 PSU L1500

GreenPerform Waterproof G3, 37.5 W, 6000 lm, 4000 K, Fixed Output, 108° x 113°

The CoreLine Waterproof G3 is a superb choice for hard-working applications. Not only does it provide excellent optical performance, it also delivers substantial energy saving. And because it works seamlessly with IoT software like Interact, it also offers the option of customisation, convenience and data-driven insights.

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP65 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	6,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	160 lm/W
Color rendering index (CRI)	80
Beam angle of light source	115 degree(s)
Light source color	White
Optic type	Very wide beam
Luminaire light beam spread	108° x 113°

Unified glare rating CEN	25
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	37.5 W
Power Factor (Fraction)	0.95
Number of products on MCB of 16 A type B	35
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	Fixed

GreenPerform Waterproof G3

Control interface	Fixed Output
Mechanical and Housing	
Housing Material	Plastic
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Grey
Optical cover finish	Textured
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Optical cover type	Polycarbonate
Net Weight (Piece)	1.700 kg
Approval and Application	
CE mark	Yes
Ambient temperature range	-30 to +50 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10%,+15%
Power consumption tolerance	+/-10%
Product Data	
Order product name	WT198C LED60S/840 PSU L1500
Full product name	WT198C LED60S/840 PSU L1500
Full product code	692234199492099
Order code	911401504747
Material Nr. (12NC)	911401504747
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341994920
Numerator - Packs per outer box	9
EAN/UPC - Case	6942730830073

Dimensional drawing

