LuxSpace Pro

DN594X LED38/CED P32PSD D200 VWB G2

LuxSpace Pro, 32 W, 3830 lm, Tunable white 2700-6500 K, DALI

Philips LuxSpace Pro builds on the LuxSpace family's reputation for superb performance, extremely low energy use, high visual comfort and appearance design. This next generation of reliable LED downlights comes in an elegant design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. LuxSpace Pro is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 450 to 8,000 lumen, 3inch to 8inch, with the option to choose fixed, dimmable, or Interact Ready variants. This makes LuxSpace Pro the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

Product data

General Information	
Light source engine type	LED
Service tag	Yes
Value ladder	Specification

Light Technical	
Luminous Flux	3,830 lm
Correlated Color Temperature (Nom)	Tunable white 2700-6500 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	>80
Light source color	Tunable White Bio-up Cyan Enhanced Spectrum CRI80
Optic type	Beam angle 60 to 120°
Unified glare rating CEN	27

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	32 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	104
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	DALI

LuxSpace Pro

Control interface	DALI

Ambient temperature range	-20 to +40 °C

Mechanical and Housing

Housing Material	Aluminum Alloy
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Optical cover finish	Matte
Overall height	125 mm
Overall diameter	212 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	1.150 kg

Approval and Application

CE mark	Yes

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	DN594X LED38/CED P32PSD D200 VWB G2
Full product name	DN594X LED38/CED P32PSD D200 VWB G2
Order code	911401506544
Material Nr. (12NC)	911401506544
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.