



GreenPerform Elite Highbay G2, 150 W, 25500 lm, Tunable White, DALI, 90°

GreenPerform Elite Highbay G2 is the latest innovation in our successful range of highbay luminaires for high ceiling and industrial applications. GreenPerform Elite Highbay G2 improves on the unique finless housing and flat optics design of earlier versions of the luminaire. Its clean and appealing aesthetic works perfectly in industrial application as well as high-ceiling applications in airports, lobbies, and other indoor areas. This versatile luminaire offers a wealth of practical features, including great light quality, exceptional energy savings, a long lifetime at an affordable price, and a wide variety of optics and lumen packages. GreenPerform Elite Highbay G2 also offers options for advanced connectivity with IoT-based systems and software applications, including Interact Pro. If you're looking for a robust, reliable, fit-and-forget solution with connectivity advantages, GreenPerform Elite Highbay G2 is the smart choice.

General Information

Number of gear units	1 unit
Gear	EBR [Electronic regulating]
Driver included	Yes
Light source engine type	LED
Value ladder	Specification
Warranty period	5 years

Light Technical

Luminous Flux	25,500 lm
Correlated Color Temperature (Nom)	Tunable White
Luminous Efficacy (rated) (Nom)	170 lm/W
Color rendering index (CRI)	>80

Number of light sources	1
Beam angle of light source	90 degree(s)
Light source color	Tunable white
Optic type	Beam angle 90°
Luminaire light beam spread	90°
Unified glare rating CEN	25
Effective projected area	0 m²

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	98 A
Inrush time	0.29 ms
Power Consumption	150 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B	4
Suitable for random switching	No
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	DALI
Control interface	DALI
Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Aluminum Alloy
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Gray
Mounting device	Suspension set simple, standard
Optical cover finish	Clear
Overall height	109 mm

Overall diameter	480 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Polycarbonate
Net Weight (Piece)	6.400 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	4.9 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	35 °C
Ambient temperature range	-30 to +50 °C

UV

UV-C radiation	0 W
UV-C irradiance defined at 0.2m	0 mW/m²


Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.3791,0.3717) SDCM < 3
Power consumption tolerance	+/-10%

Product Data

Order product name	BY778P LED255/TNW PSD WB
Full product name	BY778P LED255/TNW PSD WB
Order code	911401506548
Material Nr. (12NC)	911401506548
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	BY778P-MI-TNW.pdf	Download 

