



GreenSpace Surface Mount

SM303C P20 930 PSU WB

GreenSpace Surface Mount, 18 W, 22 W, 1800 lm, 3000 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

General Information			
Light source engine type	LED	Power Factor (Fraction)	0.9
Value ladder	Performance	Number of products on MCB of 16 A type B	-
		Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	1,800 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	90 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>90	Housing Material	Aluminum Alloy
Light source color	930 warm white	Optical cover material	Acrylate
Operating and Electrical		Housing Color	White
Input Voltage	200 to 240 V	Optical cover finish	Frosted
Line Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
Power Consumption	18 22 W	Mech. impact protection code	IK03 [0.3 J]

GreenSpace Surface Mount

Optical cover type	Acrylate
Net Weight (Piece)	1.390 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	SM303C P20 930 PSU WB
--------------------	-----------------------

Full product name	SM303C P20 930 PSU WB
Full product code	872016952918299
Order code	911401507422
Material Nr. (12NC)	911401507422
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169529182
Numerator - Packs per outer box	8
EAN/UPC - Case	8720169540675

Dimensional drawing

