



GreenSpace Surface Mount

SM303C P20 930 PSU WB

GreenSpace Surface Mount, 18 W, 22 W, 1800 lm, 3000 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

General Information		Controls and Dimming	
Light source engine type	LED	Dimmable	No
Value ladder	Performance	Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	1,800 lm	Housing Material	Aluminum Alloy
Correlated Color Temperature (Nom)	3000 K	Optical cover material	Acrylate
Luminous Efficacy (rated) (Nom)	90 lm/W	Housing Color	White
Color rendering index (CRI)	>90	Optical cover finish	Frosted
Light source color	930 warm white	Ingress protection code	IP20 [Finger-protected]
Operating and Electrical		Mech. impact protection code	IK03 [0.3 J]
Input Voltage	200 to 240 V		
Line Frequency	50 to 60 Hz		
Power Consumption	18 22 W		
Power Factor (Fraction)	0.9		
Number of products on MCB of 16 A type B	-		
Protection class IEC	Safety class II		

GreenSpace Surface Mount

Optical cover type	Acrylate
Net Weight (Piece)	1.390 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	SM303C P20 930 PSU WB
--------------------	-----------------------

Full product name	SM303C P20 930 PSU WB
Full product code	872016952918299
Order code	52918299
Material Nr. (12NC)	911401507422
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169529182
Numerator - Packs per outer box	8
EAN/UPC - Case	8720169540675

Dimensional drawing

